




PRO OFFICE SANO series ceiling lights are an efficient solution for renovating and modernising old T5/T8 louver lights. Due to slightly larger dimensions, the lights cover the old installations and so do not require the ceiling to be repainted.

Arrestor cables, plug connectors and mounting brackets make installation so easy that it can be performed by one person. In addition to ease of installation, the series offers impressive technical highlights: It provides flexible light control via CCT switch (3,000 K/4,000 K), dimmable variants (leading-edge/trailing-edge or DALI) and output adjustment in four stages (TRIAC variants only). They are also eligible for BEG German federal

Special features

- Renovation solution for T5/T8 louver lights
- Covers the old installation, therefore no repainting necessary
- Easy to install due to plug connector, arrestor cables and mounting bracket
- Light colour adjustable in two stages
- Output adjustable in four stages [TRIAC variants only]
- Eligible for BEG German federal funding for energy-efficient buildings
- Emergency power capable [176-280 V/DC EOFI: 95 %]

Housing Material	Aluminium, Stainless steel
Housing Color	White
Functions	Leuchte kann mit Gleichstrom aus einer Zentralbatterie eines Notstromsystems betrieben werden.
Protection Class	Protection class I/protective grounding
Protection Class Lamp	Protection class III/safety extra-low voltage
Power Selectable	32 W, 35.5 W, 38 W, 42 W
Rated Power Consumption Standby	0.5 W
Rated Input Voltage Frequency	198-264 V/AC 50 / 60 Hz
Power Supply Unit incl.	Yes
Dimmable	Yes
Control	Trailing-edge dimmer, Leading-edge dimmer
Motion Detector	No
Voltage range emergency lighting EOFI	176-280 V/DC 95 %
Light Source	LED, Light source not changeable
Color Temperature	3000/3500/4000 K
Colour Consistency	3 SDCM
Colour Rendering Index (Ra)	90
Rated Luminous Flux	5200/5500/5400 lm
Rated Angle of Reflection UGR	90 Degree 19
Length	1525 mm
Width	325 mm
Height	48 mm
Working Temperature	-10 to 40 °C

Storage Temperature	-10 to 40 °C
IP Protection Class	IP 40
Life Time L70 / B50	50000 h
Life Time L80 / B20	50000 h
Switching Cycles	100000
EEI	E

