



Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 5435640-5
DIP SW 8POSN AU




TE Part # 4-5435640-1
DIP SW 10 POSN SEALED



TE Part # 5161390-1
01P.DIP SWITCH ASSY



TE Part # 1977104-4
STV08=8 POS SIP SWITCH




TE Part # 3-5435640-9
DIP SW 8 POSN SEALED

Customers Also Bought



TE Part #103670-7
08 MTE HDR SRST LATCH W/HLDWN



TE Part #3-1123723-7
3.96 EP HDR ASSY 7P(BLUE)



TE Part #3-2176230-9
3522 1K2 5% 3W




TE Part #1977104-4
STV08=8 POS SIP SWITCH



TE Part #640456-2
02P MTA100 HDR ASSY F/L SQ STR




TE Part #350584-1
04P UMN L PIN HDR ASSY V2 NATL



TE Part #6-103908-5
16 MTE HDR SRST LATCH W/HLDWN



TE Part #861647-7
RECPT FLANGED HV 7 CONTACT



TE Part #1735443-2
Assembly Micro SATA Plug 7P+9P



TE Part #745783-4
25 MSFL RCPT RA 318 (IN,FM)

Documents



Product Drawings

RIGHT ANGLE DIP SW 12 P SEALED

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_2-435802-2_AK.2d_dxf.zip

English

Customer View Model

ENG_CVM_2-435802-2_AK.3d_igs.zip

English

Customer View Model

ENG_CVM_2-435802-2_AK.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2-435802-2_BW.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-435802-2_BW.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2-435802-2_BW.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English