



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**
Mating Tab Width: **7.92 mm [.312 in]**
Mating Tab Thickness: **.81 mm [.032 in]**
Terminal Orientation: **Straight**
Contact Base Material: **Brass**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	7.92 mm[.312 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	Tab-Lok
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment



Wire Insulation Support	Without
-------------------------	---------

Dimensions

Product Length	19.05 mm[.75 in]
Terminal Material Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 250 °C[-40 – 482 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece/Carton

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 60006-1
250 FASTON TAB 18-14 AWG BR

TE Part # 63771-1
187 FASTON TAB NPST

TE Part # 60006-2
250 FASTON TAB 18-14 AWG TPBR

TE Part # 63402-2
312 FASTON TAB NPST

TE Part # 41778
250 FASTON TAB 18-14 AWG TPBR

TE Part # 63953-1
187 FASTON TAB

TE Part # 626417-2
250 FASTON REC 22-18 AWG TPBR

TE Part # 42559-1
250 FASTON TAB NPST

TE Part # 61960-1
187 FASTON TAB NPST

Also in the Series | **FASTON 312**

Crimp Terminal Housings(3)

PCB Terminals(1)

Quick Disconnects(8)

Customers Also Bought



TE Part #1958292-1
KIT 12-10, 1/4, NI+RT555-1/4X1

TE Part #2066566-1
MTG BRKT-METAL LOCK, W105, ENG COMPT FRB

TE Part #132314-1
CONTACT PIN TYPE 2 SZ 16 AWG 1

TE Part #2066564-1
TOP COVER, W105, ENGINE COMPT FRB

TE Part #1-1393304-0
V23134J1052X281-EV-CBOX

TE Part #2066019-1
ECONOSEAL 15P HYBRID PLUG ASSEMBLY

TE Part #2066565-1
BOTTOM COVER, W105, ENGINE COMPT FRB

TE Part #9692543001
ACW0219-1.50-85(NS)

TE Part #CD83373001
ACW0219-1.00-2L0(NS)

TE Part #4354993001
ACW0219-4.00-7(BP)

Documents

Product Drawings
312 FASTON TAB BR

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_63402-3_K.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_63402-3_K.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_63402-3_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.