




PRO OFFICE SANO series ceiling lights are an efficient solution for renovating and modernising old T5/T8 louver lights. Due to slightly larger dimensions, the lights cover the old installations and so do not require the ceiling to be repainted.

Arrestor cables, plug connectors and mounting brackets make installation so easy that it can be performed by one person. In addition to ease of installation, the series offers impressive technical highlights: It provides flexible light control via CCT switch (3,000 K/4,000 K), dimmable variants (leading-edge/trailing-edge or DALI) and output adjustment in four stages (TRIAC variants only). They are also eligible for BEG German federal



Special features

- Renovation solution for T5/T8 louver lights
- Covers the old installation, therefore no repainting necessary
- Easy to install due to plug connector, arrestor cables and mounting bracket
- Light colour adjustable in two stages
- Output adjustable in four stages [TRIAC variants only]
- Eligible for BEG German federal funding for energy-efficient buildings
- Emergency power capable [176-280 V/DC EOFI: 95 %]

Housing Material

Aluminium, Stainless steel

Housing Color

White

Functions

Leuchte kann mit Gleichstrom aus einer Zentralbatterie eines Notstromsystems betrieben werden., Korridorfunktion mit extern verbauten DALI-Sensor.

Protection Class

Protection class I/ protective grounding

Protection Class Lamp

Protection class III/ safety extra-low voltage

Rated Input

35 W

Rated Power Consumption Standby

0.5 W

Rated Power Consumption Network Standby

0.5 W

Rated Input Voltage Frequency

198-264 V/AC 50 / 60 Hz

Power Supply Unit incl.

Yes

Dimmable

Yes

Control

DALI 2 / DT6, Push-Dim, Intelli Push-Dim

Motion Detector

No

Voltage range emergency lighting

176-280 V/DC

EOFI

95 %

Light Source

LED, Light source not changeable

Color Temperature

3000/3500/4000 K

Colour Consistency

3 SDCM

Colour Rendering Index (Ra)

90

Rated Luminous Flux

4400/4700/4600 lm

Rated Angle of Reflection

90 Degree

UGR

19

Length

625 mm

Width

625 mm

Height

48 mm

Working Temperature

-10 to 40 °C

Storage Temperature

-10 to 40 °C

IP Protection Class

IP 40

Life Time L70 / B50

50000 h

Life Time L80 / B20

50000 h

Switching Cycles

100000

EEI

F

