

GB-BTIP-N150 / GB-BTIP-N250 BRIX / Ultra Compact Mini PC



Features

- Light and simple system design and lower cost purpose
- Latest Intel® Processor
- Two storage support 1 x M.2 2280 and 1 x 2.5" SSD/HDD
- 1 x M.2 2280 PCIe Gen3x2
- Cable locking arm design to avoid cable lose

Specification

Dimension	113 x 116.52 x 56.22 mm	Front I/O	1 x Power Button 1 x USB 3.2 Gen2 Type-A 1 x USB 3.2 Gen2 with Type-C DP 1 x Headphone 1 x Microphone
MB Size	108 x 103 mm	Rear I/O	1 x HDMI 1 x RJ45 2 x USB 3.2 Gen2 Type-A 1 x USB 3.2 Gen2 with Type-C DP 1 x Wire Clamp Screw Hole
CPU	Intel® Processor N150, 4C, up to 3.6 GHz, 6W Intel® Processor N250, 4C, up to 3.8 GHz, 6W	Left I/O	1 x DC-In
Memory	1 x SO-DIMM DDR5 slot, support up to 4800MHz Max. 16GB	Right I/O	1 x Kensington lock slot
LAN	GbE LAN (Realtek® RTL8111H)	Power Supply	Input: AC 100-240V Output: DC 19V / 3.42A, 65W
Wifi Card	AW-CB515NF: WiFi 5: 802.11 a/b/g/n/ac WLAN 1T1R with Bluetooth 5.0	Support OS	Win11 64 bit
Graphics	Intel® Graphics 24 EUs / 32EUs	VESA	VESA support Supports 75 x 75 and 100 x 100 mm
Audio	Realtek® ALC897	Environment	Operating Temperature 0°C to 35°C Storage Temperature -20°C to +60°C
HDMI Resolution (Max.)	HDMI 2.0 Support 4K@60P HDR10		
Expansion Slots	1 x M.2 2280 M-key slots (PCIe Gen3x2) 1 x M.2 2230 E-key slot (For Wi-Fi + Bluetooth card)		
Storage	1 x 2.5" slot for SATA HDD/SSD		



Learn more about GIGABYTE BRIX, visit www.gigabyte.com/Mini-PcBarebone

All rights reserved. The marks mentioned herein are trademarks or registered trademarks of GIGABYTE Technology Co., Ltd. or its affiliates. All other product names mentioned herein are trademarks or registered trademarks or their respective owners. The terms HDMI and HDMI High-Definition Multimedia Interface, and the HDMI Logo are trademarks or registered trademarks of HDMI Licensing LLC in the United States and other countries.

©2024 GIGAIPC Co., Ltd.

Engineered by

GIGAIPC™