










THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



* UNLESS OTHERWISE SPECIFIED TOLERANCES
ON DECIMAL IS:

UNIT: MM			
DIM	TOL	DIM	TOL
X.	±0.15	X'	±2.0'
X.X	±0.10	X.X'	±1.0'
X.XX	±0.05	X.XX'	±0.5'
X.XXX	±0.03	X.XXX'	±0.3'

ISSUE NUMBER
ORIGINAL



NOTES:

1. MATERIAL: PHOSPHOR BRONZE C5191-1/2 H, 0.2mm THICK, PRE-PLATING TIN 50-100u" ALL OVER NICKEL 5-15u".
2. PART SHALL BE FREE OF BURRS NOT EXCEEDING 0.02mm. NO CRACKS ALLOW ON ANY SURFACES.
3. TOOLING TO BE DESIGNED WITH ADJUSTMENT TO HOLD THIS DIMENSION.
4. THE MALE TERMINAL WAS STAMPED FROM PLATING STRIP.

565-290-741	1.90±0.10	1.9±0.10	R0.55±0.05	3.0±0.10	2.7±0.10	R0.90±0.05	AWG #20-22	Ø1.70 max	8,000 X 6 R
565-290-721	1.70±0.10	1.7±0.10	R0.50±0.05	2.6±0.10	2.4±0.10	R0.83±0.05	AWG #22-28	Ø1.60 max	10,000 X 6 R
PART NO.	A1	B1	C1	A2	B2	C2	WIRE RANGE	INSULATION DIA	PCS/REEL

565 SERIES FEMALE TERMINAL



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

ACAD REFERENCE NO. 565-	
DRAWN: Peter Deng	DATE: MAY.16/15
CHECKED:	DATE:
SCALE: (IN C.A.D. 1:1)	SHEET 1 OF 1
DRAWING NUMBER	ISSUE
565-290-721 & 741	4