




Switches > DIP & SIP Switches



DIP & SIP Switch Type: **DIP**
Switch Contact Plating Material: **Gold**
Case Color: **Blue**
Case Material: **Polyester GF**
Sealed Device: **Yes**

Features

Product Type Features

DIP & SIP Switch Type	DIP
Sealed Device	Yes
Actuator Style	Rocker (Top Actuated)

Configuration Features

Number of Positions	5
Number of Switches	5
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Contact Current Rating	1 A
Operating Voltage	40 VDC

Body Features

Sealing Method	Strippable Transparent Protective Seal
Product Orientation	Vertical
Case Color	Blue
Case Material	Polyester GF



Contact Features

	30 µin
PCB Contact Termination Area Plating Material	Tin
Switch Contact Plating Material	Gold
Contact Base Material	Copper Alloy

Termination Features

Termination Post & Tail Length	3.56 mm[.14 in]
Termination Method to PCB	Through Hole - Solder

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Product Length	14.73 mm[.58 in]
Product Height	8.64 mm[.34 in]

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tube
Packaging Quantity	21

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 435668-7
LO PROFILE DIP SW 8P AU



TE Part # 3-5435668-4
DIP SW 4 POSN W/TAPE AU



TE Part # 2-5435668-8
DIP SW 8 POSN W/TAPE AU



TE Part # 2-5435668-5
DIP SW 6 POSN W/TAPE AU

Customers Also Bought



TE Part #5-641125-4
24P MTA100 ASSY P/RA SQ LF



TE Part #2-6609951-2
PSOSSDS6A=C4436




TE Part #8-1879225-4
CPF 0603 332K 0.1% 25PPM 1K RL




TE Part #254117-E
STVC 96 F ABC VVV 7-00 EE 2,9 * 247 E007



TE Part #709822-2
XCT 185-12



TE Part #87215-7
20 MODII HDR DRST UNSHRD .100



TE Part #1-1971817-3
3P,RAST 2.5 Tab Header,Ex- Locking, THV



TE Part #EM7084-000
THA-PDKG-15



Documents

Product Drawings

DIP SW 5 POSN SEALED

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_3-5435640-6_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_3-5435640-6_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_3-5435640-6_A1.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-5435640-6_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-5435640-6_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-5435640-6_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

