

Constant Voltage LED Power Supply

SLT20-12VFC-1

SLT20-24VFC-1



Product description:

This type of power supply is an exclusively designed stabilized power supply for LED lamp. With constant voltage (CV) technology, it is suitable for constant voltage lamps (12/24V DC) connected in parallels. As an advantage of constant voltage (CV) technology.

The built-in protection circuit will shut down the power supply in case of such faults as: open circuit, short circuit, over load or over temperature. The power supply will restart automatically after fault correction.



Standards:

EN61347-1
EN61347-2-13
EN61547
EN55015
EN61000-3-2
EN61000-3-3
EN62384
EN62493


Characteristics:

- Independent power supply for constant voltage LED lamp
- Special design screw terminal for field connection
- New harmonic requirements meet
- Class II protection against electric shock from direct and indirect contact
- SELV output
- Open circuit, short circuit, over load and over temperature protection
- Auto restart after fault conditions removal
- Quiet design, working noise is less than 20dB
- No load power consumption ≤ 0.5W
- Efficiency ≥ 81% (AC230V, full load)


Specifications:

Model	SLT20-12VFC-1		SLT20-24VFC-1	
Output	turn on time(S)	≤0.5	≤0.5	
	output power(W)	20	20	
	output votage(V)	12	24	
	output voltage tolerance ^①	±3%	±3%	
	ripple voltage(mV)	900(Vp-p)	1200(Vp-p)	
	working current range(A)	0-1.67	0-0.84	
	dimming interface	No		
	dimming range	n/a		
Input	rated supply voltage(Vac)	220-240	220-240	
	voltage range(Vac)	198-264	198-264	
	line frequency(Hz)	50/60	50/60	
	input current(mA)	130	130	
	efficiency ^②	≥82%@full load	≥83%@full load	
	average efficiency ^③	≥80%	≥81%	
	no load power consumption(W)	≤0.5	≤0.5	
	power factor ^②	≥0.85C@full load	≥0.85C@full load	
	inrush current(Ipk)	15A/100uS	15A/100uS	
Protection	over voltage protection	YES	YES	
	short circuit protection	YES	YES	
	over temperature protection	YES	YES	
	automatic restart	YES	YES	
	over load protection	YES	YES	
	surge capacity	L-N: 500V	L-N: 500V	
Ambient and Life	Ta(℃)	-20...45	-20...45	
	Tc max.(℃)	90	90	
	Storage Temperature(℃)	-30...80		
	ambient humidity range	5%...85%, Not condensing		
	nominal life-time(hrs)	30'000@Tc=90 C		
Other	weight(g)	70	70	
	dimensions (LxWxH)(mm)	121x45x16		
	casing material	Plastic		
	housing colour	Grey+Blue		
	type of protection	IP44		
	protection class	ClassII		
Note	1. Tolerance:includes set up tolerance, line regulation and load regulation. 2. Tested at full load,230Vac.Refer to"Power Factor" and "EFFICIENT"curve graphs. 3. Calculate the model's average efficiency for each test voltage by testing at 100%, 75%, 50%, and 25% of rated current and then computing the simple arithmetic erage of these four values. 4. All parameters NOT specially mentioned are measured at nominal voltage input, rated load and 25 of ambient temperature. 5. The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.			



Dimensions(mm):



Wiring diagram:



Electrical curves:



note

For constant current power supply, "LOAD" means the percentage of the maximum rated output voltage.
For constant voltage power supply, "LOAD" means the percentage of the maximum rated output current.

MCBS information:

Miniature circuit breaker Model	B10	B13	B16	B20	C10	C13	C16	C20
SLT20-12VFC-1 SLT20-24VFC-1	50	65	80	100	57	75	92	115

Sales & Technical Support:

SELF Electronics Co.,Ltd.(Headquarters)

Add: No. 1345 JuXian Road, Ningbo Hi Tech Park, Ningbo, China 315103
 Phone: +86-574-2880-5765, +86-574-2880-5658 (for English assistance)
 +86-574-2880-5678 (for Chinese assistance)
 Fax: +86-574-28805656
 E-mail: sales@self-electronics.com
<http://www.self-electronics.com>

SELF Electronics Co.,Ltd.,Shenzhen Office

Add: Room2007, Xinglang Xuan, Xinghemingju, Fuming Rd.,
 Futian District, Shenzhen
 Tel: +86-755-8355-8850
 Fax: +86-755-8355-8840
 E-mail: szsales@self-electronics.com

SELF Electronics Germany GmbH

August-Horch-Str. 7, 51149 Cologne
 Phone: +492203-18501-0
 Fax: 492203-18501-199
 E-mail: saleseu@self-electronics.com