

Document number: 2018 / 9C1-3578676-EN-00

Manufacturer or representative: LEDVANCE GmbH

Address: Parkring 29-33
85748 Garching
Germany

Brand name or trade mark: LEDVANCE

Product type: Luminaire

Product designation: Outdoor

☒ See attached list

The designated product(s) is (are) in conformity with the relevant Union harmonisation legislation:


- | | | |
|-------------------------------------|--------------------------------------|---|
| ☒ | 2014/35/EU
and amendments | Directive of the European Parliament and of the Council of 26 February 2014 on the harmonisation of the laws of the Member States relating to the making available on the market of electrical equipment designed for use within certain voltage limits; Official Journal of the EU L96, 29/03/2014, p. 357-374) |
| ☒ | 2014/30/EU
and amendments | Directive of the European Parliament and of the Council of 26 February 2014 on the harmonisation of the laws of the Member States relating to electromagnetic compatibility; Official Journal of the EU L96, 29/03/2014, p. 79-106 |
| ☒ | 2009/125/EC
and amendments | Directive of the European Parliament and of the Council of 21 October 2009 establishing a framework for the setting of ecodesign requirements for energy-related products |
| ☐ | 244/2009
and amendments | Commission Regulation (EC) implementing Directive 2005/32/EC of the European Parliament and of the Council with regard to ecodesign requirements for non-directional household lamps |
| ☐ | 245/2009
and amendments | Commission Regulation (EC) implementing Directive 2005/32/EC of the European Parliament and of the Council with regard to ecodesign requirements for fluorescent lamps without integrated ballast, for high intensity discharge lamps, and for ballasts and luminaires able to operate such lamps, and repealing Directive 2000/55/EC of the European Parliament and of the Council |
| ☒ | 1194/2012
and amendments | Commission Regulation (EU) No 1194/2012 of 12 December 2012 implementing Directive 2009/125/EC of the European Parliament and of the Council with regard to ecodesign requirements for directional lamps, light emitting diode lamps and related equipment |
| ☒ | 2011/65/EU
and amendments | Directive of the European Parliament and of the Council of 8 June 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment; Official Journal of the EU L174, 1/07/2011, p. 88-110 |
| ☐ | 2014/53/EU
and amendments | Directive of the European Parliament and of the Council of 16 April 2014 on the harmonisation of the laws of the Member States relating to the making available on the market of radio equipment and repealing Directive 1999/5/EC (applicable from 2016-06-13) Official Journal of the 2015/ C226/ 07 |

Last two digits of the year in which the CE marking was affixed: 19

Place and date of signatures: Foshan/ April 12nd, 2019

Signatures:


Quality Management


Quality Assurance

Names: Zhou, Stella

He, Kitty

Customer service contact: LEDVANCE GmbH, Steinerne Furt 62, 86167 Augsburg, Deutschland

This declaration of conformity is issued under the sole responsibility of the manufacturer or representative. It certifies compliance with the indicated Directives, but implies no warranty of properties.

EU Declaration of Conformity

Annex

Document number: 2018 / 9C1-3578676-EN-00

The conformity of the designated product(s) with the provisions of the European **Low Voltage Directive, 2014/35/EU**, is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- | | | |
|-------------------------------------|---|---|
| ☐ | EN 60155:
1995 + A1:1995 + A2:2007 | Glow-starters for fluorescent lamps |
| ☐ | EN 60432-1:
2000 + A1:2005 + A2:2012 | Incandescent lamps — Safety specifications — Part 1: Tungsten filament lamps for domestic and similar general lighting purposes |
| ☐ | EN 60432-2:
2000 + A1:2005 + A2:2012 | Incandescent lamps — Safety specifications — Part 2: Tungsten halogen lamps for domestic and similar general lighting purposes |
| ☐ | EN 60432-3:
2013 | Incandescent lamps — Safety specifications — Part 3: Tungsten halogen lamps (non-vehicle) |
| ☒ | EN 60598-1:
2015 | Luminaires — Part 1: General requirements and tests |
| ☒ | EN 60598-2-1:
1989 | Luminaires — Part 2-1: Particular requirements — Fixed general purpose luminaires |
| ☐ | EN 60598-2-2:
2012 | Luminaires — Part 2-2: Particular requirements — Recessed luminaires |
| ☐ | EN 60598-2-3:
2003 + A1:2011 | Luminaires — Part 2-3: Particular requirements — Luminaires for road and street lighting |
| ☐ | EN 60598-2-4:
1997 | Luminaires — Part 2-4: Particular requirements — Portable general purpose luminaires |
| ☐ | EN 60598-2-5:
2015 | Luminaires — Part 2-5: Particular requirements — Floodlights |
| ☐ | EN 60598-2-6:
1994 + A1:1997 | Luminaires — Part 2-6: Particular requirements — Luminaires with built-in transformers for filament lamps |
| ☐ | EN 60598-2-7:
1989 + A2:1996 + A13:1997 | Luminaires — Part 2-7: Particular requirements — Portable luminaires for garden use |
| ☐ | EN 60598-2-8:
2013 | Luminaires — Part 2-8 : Particular requirements — Handlamps |
| ☐ | EN 60598-2-10:
2003 | Luminaires — Part 2-10: Particular requirements — Portable luminaires for children |
| ☐ | EN 60598-2-12:
2013 | Luminaires — Part 2-12: Particular requirements — Mains socket-outlet mounted nightlights |
| ☐ | EN 60598-2-13:
2006 + A1 2012 | Luminaires — Part 2-13: Particular requirements — Ground recessed luminaires |
| ☐ | EN 60598-2-20:
2015 | Luminaires — Part 2-20: Particular requirements — Lighting chains |
| ☐ | EN 60598-2-22:
2014 | Luminaires — Part 2-22: Particular requirements — Luminaires for emergency lighting |
| ☐ | EN 60950-1: 2006 +
A11:2009 + A1:2010 +
A12:2011 + A2:2013 | Information technology equipment – Safety – Part 1: General requirements |
| ☐ | EN 60968:
2015 | Self-ballasted lamps for general lighting services — Safety requirements |
| ☐ | EN 61195:
1999 + A1:2013 + A2:2015 | Double-capped fluorescent lamps — Safety specifications |

EU Declaration of Conformity

Annex

Document number: 2018 / 9C1-3578676-EN-00

The conformity of the designated product(s) with the provisions of the European **Low Voltage Directive, 2014/35/EU**, is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

☐	EN 61199: 2011 + A2:2015	Single-capped fluorescent lamps — Safety specifications
☒	EN 61347-1: 2015	Lamp controlgear — Part 1: General and safety requirements
☐	EN 61347-2-1: 2001 + A1:2006 + A2:2014	Lamp controlgear — Part 2-1: Particular requirements for starting devices (other than glow starters)
☐	EN 61347-2-2: 2012	Lamp controlgear — Part 2-2: Particular requirements for d. c. or a. c. supplied electronic step-down convertors for filament lamps
☐	EN 61347-2-3: 2011	Lamp controlgear — Part 2-3: Particular requirements for a. c. and/or d. c. supplied electronic ballasts for fluorescent lamps
☐	EN 61347-2-7: 2012	Lamp controlgear — Part 2-7: Particular requirements for battery supplied electronic controlgear for emergency lighting (self-contained)
☐	EN 61347-2-8: 2001 + A1:2006	Lamp controlgear — Part 2-8: Particular requirements for ballasts for fluorescent lamps
☐	EN 61347-2-9: 2013	Lamp controlgear — Part 2-9: Particular requirements for ballasts for discharge lamps (excluding fluorescent lamps)
☐	EN 61347-2-10: 2001 + A1:2009	Lamp controlgear — Part 2-10: Particular requirements for electronic invertors and convertors for high-frequency operation of cold start tubular discharge lamps (neon tubes)
☐	EN 61347-2-11: 2001	Lamp controlgear — Part 2-11: Particular requirements for miscellaneous electronic circuits used with luminaires
☐	EN 61347-2-12: 2005 + A1:2010	Lamp controlgear — Part 2-12: Particular requirements for d. c. or a. c. supplied electronic ballasts for discharge lamps (excluding fluorescent lamps)
☒	EN 61347-2-13: 2014	Lamp controlgear — Part 2-13: Particular requirements for d. c. or a. c. supplied electronic controlgear for LED modules
☐	EN 61549: 2003 + A1:2005 + A2:2010 + A3:2012	Miscellaneous lamps
☒	EN 62031: 2008 + A1:2013 + A2:2015	LED modules for general lighting — Safety specifications
☐	EN 62034: 2012	Automatic test systems for battery powered emergency escape lighting
☐	EN 62035: 2014	Discharge lamps (excluding fluorescent lamps) — Safety specifications
☐	EN 62368-1: 2014	Audio/video, information and communication technology equipment – Part 1: Safety requirements

EU Declaration of Conformity

Annex

Document number: 2018 / 9C1-3578676-EN-00

The conformity of the designated product(s) with the provisions of the European **Low Voltage Directive, 2014/35/EU** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- | | | |
|-------------------------------------|---|---|
| ☒ | EN 62493:
2010 | Assessment of lighting equipment related to human exposure to electromagnetic fields |
| ☐ | EN 62532:
2011 | Fluorescent induction lamps — Safety specifications |
| ☐ | EN 62560:
2012 + A1:2015 | Self-ballasted LED-lamps for general lighting services by voltage > 50 V — Safety specifications |
| ☐ | EN 62838:
2016 | LEDs lamps for general lighting services with supply voltages not exceeding 50 V a.c. r.m.s. or 120 V ripple free d.c. - Safety specifications
Consumer goods with a voltage below 50 V are dealt with by the General Product Safety Directive (GPSD) 2001/95/EC |
| ☐ | EN 60669-2-1:
2004 + A1:2009 + A12:2010 | Switches for household and similar fixed electrical installations - Part 2-1: Particular requirements - Electronic switches (IEC 60669-2-1:2002, modified) / Corrected and reprinted in 2007-12 |
| ☐ | EN 62471:
2008 | Photobiological safety of lamps and lamp systems |
| ☐ | EN 62733:
2015 | Programmable components in electronic lamp controlgear |
| ☐ | EN 62776:
2015 | Double-capped LED lamps designed to retrofit linear fluorescent lamps - Safety specifications |
| ☐ | EN 60598-2-24:
2013 | Luminaires - Part 2-24: Particular requirements - Luminaires with limited surface temperatures |
| ☐ | | |

EU Declaration of Conformity

Annex

Document number: 2018 / 9C1-3578676-EN-00

The conformity of the designated product(s) with the provisions of the European **EMC Directive, 2014/30/EU** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- | | | |
|-------------------------------------|------------------------------|---|
| ☒ | EN 55015:
2013 | Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment |
| ☒ | EN 61000-3-2:
2014 | Electromagnetic compatibility (EMC) — Part 3-2: Limits — Limits for harmonic current emissions (equipment input current ≤ 16 A per phase) |
| ☒ | EN 61000-3-3:
2013 | Electromagnetic compatibility (EMC) — Part 3-3: Limits — Limitation of voltage changes, voltage fluctuations and flicker in public low voltage supply systems, for equipment with rated current ≤ 16 A per phase and not subjected to conditional connection |
| ☒ | EN 61547:
2009 | Equipment for general lighting purposes — EMC immunity requirements |
| ☐ | EN 50498: 2010 | Electromagnetic compatibility (EMC) –
Product family standard for aftermarket electronic equipment in vehicles |
| ☐ | | |

EU Declaration of Conformity Annex

Document number: 2018 / 9C1-3578676-EN-00

The conformity of the designated product(s) with the provisions of the European **eco design (ERP) Directive** is given by the compliance with the following European Standard(s). If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- ☐ **EN 62442-1:**
2011 Energy performance of lamp controlgear - Part 1: Controlgear for fluorescent lamps - Method of measurement to determine the total input power of controlgear circuits and the efficiency of the controlgear
- ☐ **EN 62442-2:**
2014 Energy performance of lamp controlgear –
Part 2: Controlgear for high intensity discharge lamps (excluding fluorescent lamps) – Method of measurement to determine the efficiency of the controlgear
- ☐ **EN 62442-3:**
2014 Energy performance of lamp controlgear –
Part 3: Controlgear for halogen lamps and LED modules – Method of measurement to determine the efficiency of the controlgear
- ☐

EU Declaration of Conformity Annex

Document number: 2018 / 9C1-3578676-EN-00

The conformity of the designated product(s) with the provisions of the European Directive **RoHS** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- ☒ **EN 50581:**
2012 Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances
- ☐

EU Declaration of Conformity

Annex

Document number: 2018 / 9C1-3578676-EN-00

The conformity of the designated product(s) with the provisions of the European **radio equipment Directive** is given by the compliance with the following European Standard(s). If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- | | | |
|--------------------------|--|--|
| ☐ | EN 300 328 V2.1.1 | Wideband transmission systems; Data transmission equipment operating in the 2,4 GHz ISM band and using wide band modulation techniques; Harmonised Standard covering the essential requirements of article 3.2 of Directive 2014/53/EU |
| ☐ | Draft ETSI EN 301 489-1 V2.2.0 | Electro Magnetic Compatibility (EMC) standard for radio equipment and services; Part 1: Common technical requirements; Harmonised Standard covering the essential requirements of article 3.1(b) of Directive 2014/53/EU and the essential requirements of article 6 of Directive 2014/30/EU |
| ☐ | Draft ETSI EN 301 489-17 V3.2.0 | Electro Magnetic Compatibility (EMC) standard for radio equipment and services; Part 17: Specific conditions for Broadband Data Transmission Systems; Harmonised Standard covering the essential requirements of article 3.1(b) of Directive 2014/53/EU |
| ☐ | EN 62479: 2010 | Assessment of the compliance of low-power electronic and electrical equipment with the basic restrictions related to human exposure to electromagnetic fields (10 MHz to 300 GHz) |
| ☐ | | |

EU Declaration of Conformity

Attached list

Document number: 2018 / 9C1-3578676-EN-00

AC02217	ENDURA STYLE Cylinder Wall 6W ST
AC02218	ENDURA STYLE Cylinder Wall Sensor 6W ST
AC02219	ENDURA STYLE Cylinder 50CM 6W ST
AC02220	ENDURA STYLE Cylinder 80CM 6W ST
AC02221	ENDURA STYLE Cylinder Ceiling 6W ST