

☒ See attached list

EU Declaration of Conformity
Annex

Document number: 2017 / 9C1-3434453-EN-01

The conformity of the designated product(s) with the provisions of the European **Low Voltage Directive, 2014/35/EU**, is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

☐	EN 60155: 1995 + A1:1995 + A2:2007	Glow-starters for fluorescent lamps
☐	EN 60432-1: 2000 + A1:2005 + A2:2012	Incandescent lamps — Safety specifications — Part 1: Tungsten filament lamps for domestic and similar general lighting purposes
☐	EN 60432-2: 2000 + A1:2005 + A2:2012	Incandescent lamps — Safety specifications — Part 2: Tungsten halogen lamps for domestic and similar general lighting purposes
☐	EN 60432-3: 2013	Incandescent lamps — Safety specifications — Part 3: Tungsten halogen lamps (non-vehicle)
☒	EN 60598-1: 2015	Luminaires — Part 1: General requirements and tests
☒	EN 60598-2-1: 1989	Luminaires — Part 2-1: Particular requirements — Fixed general purpose luminaires
☐	EN 60598-2-2: 2012	Luminaires — Part 2-2: Particular requirements — Recessed luminaires
☐	EN 60598-2-3: 2003 + A1:2011	Luminaires — Part 2-3: Particular requirements — Luminaires for road and street lighting
☐	EN 60598-2-4: 1997	Luminaires — Part 2-4: Particular requirements — Portable general purpose luminaires
☐	EN 60598-2-5: 2015	Luminaires — Part 2-5: Particular requirements — Floodlights
☐	EN 60598-2-6: 1994 + A1:1997	Luminaires — Part 2-6: Particular requirements — Luminaires with built-in transformers for filament lamps
☐	EN 60598-2-7: 1989 + A2:1996 + A13:1997	Luminaires — Part 2-7: Particular requirements — Portable luminaires for garden use
☐	EN 60598-2-8: 2013	Luminaires — Part 2-8 : Particular requirements — Handlamps
☐	EN 60598-2-10: 2003	Luminaires — Part 2-10: Particular requirements — Portable luminaires for children
☐	EN 60598-2-12: 2013	Luminaires — Part 2-12: Particular requirements — Mains socket-outlet mounted nightlights
☐	EN 60598-2-13: 2006 + A1 2012	Luminaires — Part 2-13: Particular requirements — Ground recessed luminaires
☐	EN 60598-2-20: 2015	Luminaires — Part 2-20: Particular requirements — Lighting chains
☐	EN 60598-2-22: 2014	Luminaires — Part 2-22: Particular requirements — Luminaires for emergency lighting
☐	EN 60598-2-24: 2013	Luminaires - Part 2-24: Particular requirements - Luminaires with limited surface temperatures
☐	EN 60950-1: 2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013	Information technology equipment – Safety – Part 1: General requirements
☐	EN 60968: 2015	Self-ballasted lamps for general lighting services — Safety requirements
☐	EN 61195: 1999 + A1:2013 + A2:2015	Double-capped fluorescent lamps — Safety specifications

EU Declaration of Conformity
Annex

Document number: 2017 / 9C1-3434453-EN-01

The conformity of the designated product(s) with the provisions of the European **Low Voltage Directive, 2014/35/EU**, is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

☐	EN 61199: 2011 + A2:2015	Single-capped fluorescent lamps — Safety specifications
☒	EN 61347-1: 2015	Lamp controlgear — Part 1: General and safety requirements
☐	EN 61347-2-1: 2001 + A1:2006 + A2:2014	Lamp controlgear — Part 2-1: Particular requirements for starting devices (other than glow starters)
☐	EN 61347-2-2: 2012	Lamp controlgear — Part 2-2: Particular requirements for d. c. or a. c. supplied electronic step-down convertors for filament lamps
☐	EN 61347-2-3: 2011	Lamp controlgear — Part 2-3: Particular requirements for a. c. and/or d. c. supplied electronic ballasts for fluorescent lamps
☐	EN 61347-2-7: 2012	Lamp controlgear — Part 2-7: Particular requirements for battery supplied electronic controlgear for emergency lighting (self-contained)
☐	EN 61347-2-8: 2001 + A1:2006	Lamp controlgear — Part 2-8: Particular requirements for ballasts for fluorescent lamps
☐	EN 61347-2-9: 2013	Lamp controlgear — Part 2-9: Particular requirements for ballasts for discharge lamps (excluding fluorescent lamps)
☐	EN 61347-2-10: 2001 + A1:2009	Lamp controlgear — Part 2-10: Particular requirements for electronic invertors and convertors for high-frequency operation of cold start tubular discharge lamps (neon tubes)
☒	EN 61347-2-11: 2001	Lamp controlgear — Part 2-11: Particular requirements for miscellaneous electronic circuits used with luminaires
☐	EN 61347-2-12: 2005 + A1:2010	Lamp controlgear — Part 2-12: Particular requirements for d. c. or a. c. supplied electronic ballasts for discharge lamps (excluding fluorescent lamps)
☐	EN 61347-2-13: 2014	Lamp controlgear — Part 2-13: Particular requirements for d. c. or a. c. supplied electronic controlgear for LED modules
☐	EN 61549: 2003 + A1:2005 + A2:2010 + A3:2012	Miscellaneous lamps
☒	EN 62031: 2008 + A1:2013 + A2:2015	LED modules for general lighting — Safety specifications
☐	EN 62034: 2012	Automatic test systems for battery powered emergency escape lighting
☐	EN 62035: 2014	Discharge lamps (excluding fluorescent lamps) — Safety specifications
☐	EN 62368-1: 2014	Audio/video, information and communication technology equipment – Part 1: Safety requirements

EU Declaration of Conformity
Annex

Document number: 2017 / 9C1-3434453-EN-01

The conformity of the designated product(s) with the provisions of the European **Low Voltage Directive, 2014/35/EU** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- ☒ **EN 62493:**
2015
- Assessment of lighting equipment related to human exposure to electromagnetic fields
- ☐ **EN 62532:**
2011
- Fluorescent induction lamps — Safety specifications
- ☐ **EN 62560:**
2012 + A1:2015
- Self-ballasted LED-lamps for general lighting services by voltage > 50 V — Safety specifications
- ☐ **EN 62838:**
2016
- LEDsi lamps for general lighting services with supply voltages not exceeding 50 V a.c. r.m.s. or 120 V ripple free d.c. - Safety specifications
Consumer goods with a voltage below 50 V are dealt with by the General Product Safety Directive (GPSD) 2001/95/EC
- ☐ **EN 60669-2-1:**
2004 + A1:2009 + A12:2010
- Switches for household and similar fixed electrical installations - Part 2-1: Particular requirements - Electronic switches (IEC 60669-2-1:2002, modified) / Corrected and reprinted in 2007-12
- ☒ **EN 62471:**
2008
- Photobiological safety of lamps and lamp systems
- ☐ **EN 62733:**
2015
- Programmable components in electronic lamp controlgear
- ☐ **EN 62776:**
2015
- Double-capped LED lamps designed to retrofit linear fluorescent lamps - Safety specifications
- ☐

EU Declaration of Conformity
Annex

Document number: 2017 / 9C1-3434453-EN-01

The conformity of the designated product(s) with the provisions of the European **EMC Directive, 2014/30/EU** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

☒	EN 55015: 2013	Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment
☐	EN 61000-3-2: 2014	Electromagnetic compatibility (EMC) — Part 3-2: Limits — Limits for harmonic current emissions (equipment input current ≤ 16 A per phase)
☐	EN 61000-3-3: 2013	Electromagnetic compatibility (EMC) — Part 3-3: Limits — Limitation of voltage changes, voltage fluctuations and flicker in public low voltage supply systems, for equipment with rated current ≤ 16 A per phase and not subjected to conditional connection
☒	EN 61547: 2009	Equipment for general lighting purposes — EMC immunity requirements
☐	EN 50498: 2010	Electromagnetic compatibility (EMC) – Product family standard for aftermarket electronic equipment in vehicles
☐		

EU Declaration of Conformity
Annex

Document number: 2017 / 9C1-3434453-EN-01

The conformity of the designated product(s) with the provisions of the European **eco design (ERP) Directive** is given by the compliance with the following European Standard(s). If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- ☐ **EN 62442-1:**
2011
- Energy performance of lamp controlgear - Part 1: Controlgear for fluorescent lamps - Method of measurement to determine the total input power of controlgear circuits and the efficiency of the controlgear
- ☐ **EN 62442-2:**
2014
- Energy performance of lamp controlgear –
Part 2: Controlgear for high intensity discharge lamps (excluding fluorescent lamps) – Method of measurement to determine the efficiency of the controlgear
- ☐ **EN 62442-3:**
2014
- Energy performance of lamp controlgear –
Part 3: Controlgear for halogen lamps and LED modules – Method of measurement to determine the efficiency of the controlgear

☐

EU Declaration of Conformity
Annex

Document number: 2017 / 9C1-3434453-EN-01

The conformity of the designated product(s) with the provisions of the European Directive **RoHS** is given by the compliance with the following European Standard(s) or other specifications. If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- ☒ **EN 50581:**
2012
- Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances
- ☐

EU Declaration of Conformity
Annex

Document number: 2017 / 9C1-3434453-EN-01

The conformity of the designated product(s) with the provisions of the European **radio equipment Directive** is given by the compliance with the following European Standard(s). If not elsewhere/otherwise indicated the edition/amendment as referenced below applies.

- ☐ EN 300 328 V2.1.1
- Wideband transmission systems; Data transmission equipment operating in the 2,4 GHz ISM band and using wide band modulation techniques; Harmonised Standard covering the essential requirements of article 3.2 of Directive 2014/53/EU
- ☐ EN 300 440 V2.1.1&V2.2.
- Short Range Devices (SRD) ; Radio equipment to be used in the 1GHz to 40GHz frequency range; Harmonised Standard covering the essential requirements of article 3.2 of Directive 2014/53/EU
- ☐ Draft ETSI EN 301 489-1 V2.2.0
- Electro Magnetic Compatibility (EMC) standard for radio equipment and services; Part 1: Common technical requirements; Harmonised Standard covering the essential requirements of article 3.1(b) of Directive 2014/53/EU and the essential requirements of article 6 of Directive 2014/30/EU
- ☐ Draft EN 301 489-3 V2.1.1
- ElectroMagnetic Compatibility (EMC) standard for radio equipment and services; Part 3: Specific conditions for Short-Range Devices (SRD) operating on frequencies between 9 kHz and 246 GHz; Harmonised Standard covering the essential requirements of article 3.1(b) of Directive 2014/53/EU
- ☐ Draft ETSI EN 301 489-17 V3.2.0
- Electro Magnetic Compatibility (EMC) standard for radio equipment and services; Part 17: Specific conditions for Broadband Data Transmission Systems; Harmonised Standard covering the essential requirements of article 3.1(b) of Directive 2014/53/EU
- ☐ EN 62479: 2010
- Assessment of the compliance of low-power electronic and electrical equipment with the basic restrictions related to human exposure to electromagnetic fields (10 MHz to 300 GHz)
- ☐

EU Declaration of Conformity
Attached list

Document number: 2017 / 9C1-3434453-EN-01

- AC01664-NIGHTLUX Ceiling White
- AC01958-NIGHTLUX Ceiling Silver