

PCJ-124D3MH,301

✕ OBSOLETE

OEG

TE Internal #: 1-1721081-4

TE Internal Description: PCJ-124D3MH,301

Slim PCB Relay, PCN 3A/5A 3VDC

[View on TE.com >](#)



All Slim PCB Relay, PCN 3A/5A 3VDC (0)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought



TE Part #1-825433-2
MOD 2 PINHDR 1X12P.



TE Part #5787082-2
26 50SR R/A RCPT ASSY,RDSN L/F



TE Part #5650466-5
ASSEMBLY,RECEPTACLE,EURO,TYPE



TE Part #1614354-2
RN 0603 4K22 0.1% 10PPM CUT LENGTH



TE Part #3-1614350-9
RN 0603 14K 0.1% 10PPM CUT LENGTH




TE Part #8-1614884-0
CPF 0805 6K8 0.1% 25PPM 1K RL



TE Part #1676290-1
RN 0805 2K49 0.1% 10PPM CUT LENGTH



TE Part #6-2176093-1
RP 2A 0.25W 43K2 0.1% 25PPM 1K RL



TE Part #1-216602-2
12P HV190 FEDERLEIS



TE Part #1879022-1
SMF3 330R 5%

Documents

Product Drawings

PCJ-124D3MH,301

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1721081-4_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1721081-4_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1721081-4_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages
PCJ Series Relay Data Sheet English
English

Product Specifications
Product Specification
Japanese
Definitions General Purpose Relays
English