

VOLTCRAFT - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

CSP-140 **Laboratory Power Supply**

CE

Item no: 3438793

A laboratory power supply for low-voltage units developed for universal use in the research, development, manufacturing, service and training fields.



TECHNICAL DATA

Power supply	85 - 265 V/AC 50/60 Hz
Output voltage	±15 V/DC
Output current	max. 1 A
Load regulation	50 mV
Line regulation	5 mV
Ripple and noise	3 mVrms
Output accuracy	±5 %
Short-circuit protection	Yes
Overcurrent protection	Yes
Protection class	II
Operation time	max. 8 hours
Fuse	T1.5AL250V
Power cord length	1.5 m
Operating temperature	0 to +40 °C
Operating humidity	20 - 85 %
Storage temperature	0 to +40 °C
Storage humidity	20 - 85 %
Dimensions (W x H x D)	110 × 74 × 140 mm
Weight	300 g

CONTENTS

Main unit // Mains cable // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*3438793_V1_0126_en_ds 2673255051 I1/O1 en