


29320102	DATA SHEET
Valid from: 08.11.2018	GOF SIMPLEX Pigtail ST G62,5, 2m

Description

- GOF Optical fiber Pigtail
- ST-Simplex-plug on open cable head



General characteristics

Connection method, connector
Polishing
Cable type
Number of fibers
Fiber color (acc. IEC 60304)

ST-Simplex (ST-S)
PC (physical contact)
Pigtail
12
Red, green, blue, yellow, white, grey, brown, violet, turquoise, black, orange, pink
-25 °C to +70 °C (-13 °F to 158 °F) (Operation)
-25 °C to +70 °C (-13 °F to 158 °F) (Storage)
-10 °C to +60 °C (-10 °F to 140 °F) (Installation)

Temperature range

Variation

Article	Description	Fiber type
29320102	GOF SIMPLEX Pigtail ST G62,5, 2m	Multimode 62.5 µm
29320202	GOF SIMPLEX Pigtail ST G50 OM2, 2m	Multimode OM2 50 µm
29320302	GOF SIMPLEX Pigtail ST G50 OM3, 2m	Multimode OM3 50 µm
29320402	GOF SIMPLEX Pigtail ST G50 OM4, 2m	Multimode OM4 50 µm

Additional note

Standard length 2m. Data sheet also valid for variant lengths.

Optical properties

Insertion loss (max.)	0,25 dB / 0,5 dB (mean/97%)
Return loss (min.)	45 dB

Mechanical properties

ST-S-Plug


Housing, material	Hpb59-1, grey
Boot, material	TPE, black
Ferrule, material	Zirconia
Ferrule-Ø	2.5 mm
Tensile strength	5 N
Mating cycles (min.)	1000

Line

Outer coating, material	LSOH
Bending radius (min.)	50 mm (Installation) 25 mm (Operation)

29320102	DATA SHEET
Valid from: 08.11.2018	GOF SIMPLEX Pigtail ST G62,5, 2m

Technical drawing



Standards / Approvals

Fibre optic connector interfaces – Type BFOC/2,5	IEC 61754-2
Optical fibres – part 2-10: category A1 multimode fibres	IEC 60793-2-10
Standard colours for insulation for low-frequency cables and wires	IEC 60304

Application range

Office, Data centers, Industry

Note

Photographs are not true to scale and do not represent detailed images of the respective products.