

21700120	DATA SHEET	
Valid from: 17.06.2020	ETHERLINE ACCESS U16T	

Description

- Fast Ethernet Network-Switch (10/100BaseT(X)), unmanaged
- Ports: 16x RJ45
- Suitable for harsh industrial environment (Protection class IP30)



General characteristics

Interfaces & buttons

RJ45 Port: 10/100BaseT(X) auto-negotiation, full-/halfduplex-mode and Auto-MDI/MDI-X-connection
DIP-switch: Activate/deactivate the Broadcast Storm Protection

Switch properties

MAC- table size: 8 K
packet-buffer size: 2 Mbit
operating temp.: -10°C to +60°C (14°F to 140°F)
storage temp.: -40°C to +85°C (-40°F to 185°F)
5% to 95 % (non-condensing)

Temperature range

Relative humidity

Standards

IEEE 802.3i (10BaseT)
IEEE 802.3u (100BaseTX)

Processing type

Store and Forward

MTBF (mean time between failures)

1.889.468 Std @ Telcordia (Bellcore), GB

Power requirements

Connection

1 removable 4- pole terminal block

Input voltage

24 V AC /V DC (18-30V AC, 50/60Hz; 12-48V DC)

Power Consumption (max.)

8 W

Input current (max.)

0.70 A

Overload current protection

support

Reverse polarity protection

support

Redundancy protection

support

Physical properties

Housing

metal

IP class

IP30

Weight

0.7 kg

Installation


DIN-rail mounting

Creator: FELI1/PDP Released: IVSE1/PDP	Dokument: DB21700120EN Version: 00	Page 1 of 2
---	---------------------------------------	-------------

21700120	DATA SHEET	
Valid from: 17.06.2020	ETHERLINE ACCESS U16T	

Technical drawing

Dimensional drawing



Standards and approvals

Safety
EMC
EMI
EMS

Vibration
Shock
Free fall
Approvals

UL61010
EN55022/CISPR22 Class A
FCC CFR47 Part 15
IEC 61000-4-2 ESD: contact: 6kV / air: 8kV
IEC 61000-4-3 RS: 80Mhz to 2GHz: 10V/m
IEC 61000-4-4 EFT/Burst: Power: 2kV / Signal: 1kV
IEC 61000-4-5 Surge: Power: 1kV / Signal: 1kV
IEC 61000-4-6 CS: 10V (150 kHz – 80 MHz)
according IEC 60068-2-6
according IEC 60068-2-27
according IEC 60068-2-31
CE
UL (E331560)
FCC

Application range

Automation, industrial machinery and plant engineering

Note

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: FELI1/PDP Released: IVSE1/PDP	Dokument: DB21700120EN Version: 00	Page 2 of 2
---	---------------------------------------	-------------