

44428226	DATA SHEET	
Valid from: 15.12.2023	EPIC® SOLAR 4 Splitter	

1. EPIC® SOLAR 4 Splitter

connector for photovoltaic applications for parallel connection of strings

EPIC® SOLAR 4 Splitter MFF

44428226



EPIC® SOLAR 4 Splitter FMM

44428227




Creator: S. Koch /PDs Released: IVSE1/PDP	Document: DB44428226EN Version: 02	Page 1 of 3
--	---------------------------------------	-------------

44428226	DATA SHEET	
Valid from: 15.12.2023	EPIC® SOLAR 4 Splitter	

2. Electrical data's

Rated voltage	1000V DC
Rated current	30,0A (85°C)
Rated impulse voltage	III
Rated voltage	6 kV
Protection class	II
Contact resistance	<2,0mΩ

3. Derating curve



44428226	DATA SHEET	
Valid from: 15.12.2023	EPIC® SOLAR 4 Splitter	

4. General Data

Protection class IP 65 / IP67

Degree of contamination 3

Temperature range -40°C ... +85°C

Limit temperature 105°C

to open without tool

Cycle rate 100

5. Materials

Insulation body PPO

Flammability UL94 V-0

Sealing FKM

6. Certification

RoHS conform

7. Standards

EN 50521 Connectors for photovoltaic systems – Safety requirements and tests

Creator: S. Koch /PDs Released: IVSE1/PDP	Document: DB44428226EN Version: 02	Page 3 of 3
--	---------------------------------------	-------------