



TOOLCRAFT

DATASHEET

ESD Analogue Soldering Station - 70 W 480 °C

Item No. 3411542



Features

- Includes sleep mode and temperature preset function
- Temperature range: +160 to +480 °C
- Rapid heating (heating time 10 s to 300 °C)
- Standby mode temperature 200 °C
- Temperature control knob with indicator light indicating the temperature status in real time
- Automatically switches to standby mode if not used for 5 minutes
- Soldering iron cable length 1.1 m



Technical data

Main unit

Input voltage	220 - 240 V/AC, 50 Hz
Power consumption	70 W
Protection class	I
ESD safe	Yes
Temperature units	°C / °F
Temperature range	+160 to +480 °C
Operating conditions	0 to +40 °C, 20 - 70 % RH
Storage conditions	0 to +45 °C, 5 - 80 % RH
Cable length	1.25 m
Dimensions (W x H x D)	115 x 92 x 157 mm
Weight	1.59 kg

Soldering iron

Input	20 V/DC
Power consumption	70 W
Temperature range	160 - 480 °C, (320 - 896 °F)
Heating time	10 s to 300 °C
Cable length	approx. 1.1 m
Dimensions (Ø x L)	19 x 220 mm
Weight	approx. 90 g

Soldering iron holder

Dimensions (W x H x D)	60 x 90 x 160 mm
Weight	approx. 238 g

Solder wire spool holder

Dimensions (W x H x D)	78 x 63 x 45 mm
Weight	74 g



Delivery content

- Main unit
- Soldering Iron
- Soldering iron stand
- Sponge
- Wire cleaning ball
- Solder wire spool holder
- Mains cable
- Operating instructions