VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry.
We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

DIGITAL OSCILLOSCOPE

CE

Item no. 3451430 (ADO1002) // 100 MHz
Item no. 3451431 (ADO3504) // 350 MHz
Item no. 3451429 (ADO5004) // 500 MHz

FEATURES

Max. 2.5 GSa/s sample rate // 250M record length // RS232/UART, I2C, SPI, LIN, CAN decoding //
25.65 cm (10.1 inch) touchscreen //



Image shows Item no. 3451429

PACKAGE CONTENTS

Oscilloscope // Power cord // USB cable // 2x Probes + adjustment set (for 2 channel models) // 4x Probes+ adjustment set (for 4 channel models) // Operating instructions

TECHNICAL DATA

Oscilloscope

Vertical System

Analog Channel

Characteristics	Instruction	
Input Coupling	DC, AC, Ground	
Input Impedance	1 MΩ±2%, parallel with 15 pF±5 pF, 50Ω ± 2%	
Probe attenuation coefficient setting	Common	10.00μX,20.00μX,50.00μX,100.00μX, 200.00μX,500.00μX,1.00mX,2.00mX, 5.00mX,10.00mX,20.00mX,50.00mX, 100.00mX,200.00mX,500.00mX,1.00X, 2.00X,5.00X,10.00X,20.00X,50.00X, 100.00X,200.00X,500.00X,1.00kX,2.00kX, 5.00kX,10.00kX,20.00kX, 50.00kX
	Custom	1.00μX - 1.00MX
Maximum Input Voltage	1MΩ: ≤300 Vrms 50Ω: ≤5 Vrms	
Vertical Resolution	12 bits	
Vertical Sensitivity	500 μV/div ~ 10 V/div [1]	
Displacement	±2 V (500μV/div – 50 mV/div) ±20 V (100 mV/div – 500 mV/div) ±200 V (1 V/div – 10 V/div)	
Analog bandwidth	ADO1002	100 MHz
	ADO3504	350 MHz
	ADO5004	500 MHz
Single bandwidth	Full bandwidth	
Low Frequency (AC coupling, -3dB)	≥10 Hz (at BNC)	
Rising Time(at BNC, typical)	ADO1002	≤3.5 ns
	ADO3504	≤1 ns
	ADO5004	≤0.7 ns
DC Gain Accuracy	≤1 mV	3%
	2 mV	2%
	≥5 mV	1.5%
DC accuracy (average)	Delta Volts between any two averages of ≥16 waveforms acquired with the same scope setup and ambient conditions (△V): ±(3% rdg + 0.05 div)	
Channel–channel isolation	50 Hz: 100:1 10 MHz: 40:1	
Time delay between channel(typical)	150 ps	
Waveform inverted	Support	
Bandwidth limit	20 MHz, full bandwidth	

Description:
[1]: 500 μV/div is a digital magnification of 1mV/div.
Horizontal System

Horizontal System

Analog Channel

Characteristics	Instruction
Scanning speed (s/div)	500 ps/div - 1000s/div, step by 1-2-5
Time base accuracy	±1 ppm (typical value, ambient temperature: +25℃)
Time interval (△T) measurement accuracy (DC ~ 100MHz)	Single: ±(1 interval time+|time base accuracy|×reading+0.6 ns) Average>16: ±(1 interval time +|time base accuracy|×reading+0.4 ns)
Sampling rate range	0.05 Sa/s ~ 2.5 GSa/s
Maximum Storage Depth	250M

Acquire System

Characteristics	Instruction		
Acquire mode	Sample, Peak, High Res, Average, Segmentation		
Maximum real-time acquire rate	ADO1002	Dual Channel	1.25 GSa/s
		Single Channel	2.5 GSa/s
	ADO3504 ADO5004	Four Channel, Dual Channel[1]	1.25 GSa/s
		Dual Channel[2]	2.5 GSa/s
		Single Channel	2.5 GSa/s
Waveform capture rate	Real-time acquire: 50,000 wfms/s Segment acquire: 500,000 wfms/s		
Record length	1k,10k,100k,1M,10M,100M,250M		
	Note: The record length is dynamic, changing with the acquire mode		
Interpolation	Auto, Sinx/x, x		

Description:

[1] : Limited to four-channel models, the maximum real-time sampling rate of dual channels must be one of the following conditions: CH1 and CH2 are both on, or CH3 and CH4 are both on.

[2]: Limited to four-channel models, the maximum real-time sampling rate of two channels should meet one of the following conditions: only one channel of CH1 and CH2 can be turned on, and only one channel of CH3 and CH4 can be turned on.

Trigger

Trigger System

Characteristics	Instruction	
Trigger source	CH1, CH2, CH3, CH4, EXT TRIG, AC Lines	
Trigger mode	Auto, Normal, Single	
Trigger type	Edge trigger, Video trigger, Pulse trigger, Slope trigger, Runt trigger, Windows trigger, Timeout trigger, Nth trigger, Logic trigger, RS232/UART trigger, I2C trigger, SPI trigger, CAN trigger, LIN trigger	
50% level setting (typical)	Input signal frequency ≥ 50 Hz	
Holdoff range	100 ns to 10s	
Trigger sensitivity	0.3 div ~ 10 div	
Trigger offset range	Internal	±5 divs from the center of the screen
	EXT	±2V
	EXT/5	±10V

Trigger Type

Characteristics	Instruction	
Edge Trigger	Couple	DC, AC, HF
	Slope	Rising, Falling
Video Trigger	Modulation	Support standard NTSC, PAL and SECAM broadcast systems
	Line number range	1-525 (NTSC) and 1-625 (PAL/SECAM)
Pulse Trigger	Trigger condition	Positive pulse: >, <, = Negative pulse: >, <, =
	Pulse Width range	30 ns to 10 s
Slope Trigger	Trigger condition	Positive pulse: >, <, = Negative pulse: >, <, =
	Time setting	30 ns to 10 s
Runt Trigger	Trigger condition	Positive pulse: >, <, = Negative pulse: >, <, =
	Time setting	30 ns to 10 s
Windows Trigger	Trigger condition	Positive pulse: superamplitude entry, superamplitude exit, and superamplitude time Negative pulse: superamplitude entry, superamplitude exit, and superamplitude time
	Time setting	30 ns ~ 10 s
Timeout Trigger	Slope	Rising, Falling
	Idle Time	30 ns ~ 10 s
The Nth Edge Trigger	Slope	Rising, Falling
	Idle Time	30 ns ~ 10 s
	Edge Number	1 ~ 128
Logic trigger	Logic Mode	AND, OR, XOR,XNOR
	Input Mode	H, L, X, Rising, Falling
	Output Mode	Goes True, Goes False, Is True >, Is True <, Is True =
RS232/UART Trigger	Polarity	Normal, Inverted
	Trigger Condition	Start, Error, Chk Error, Data
	Baud Rate	Common, Custom
	Data Bits	5 bits, 6 bits, 7 bits, 8 bits
I2C Trigger	Trigger Condition	Start, Restart, Stop, Ack Lost, Addr, Data, Addr/Data
	Address Range /Byte Length	7 bits---->0 to 127 8 bits---->0 to 255 10 bits--->0 to 1023

	ByteLength	1 to 5
SPI Trigger	Trigger Condition	Timeout
	Timeout value	30 ns to 10s
	Data Bits	4 bits to 32 bits
	Edge	Rising, Falling
CAN Trigger	Signal Type	CAN_H, CAN_L, TX, RX, DIFF
	Trigger Condition	Start, Type, Data, ID, ID/Data, End, Lost, Error
	Baud Rate	Common, Custom
	Sample Point	0.5% to 95%
	Frame Type	Data, Remote, Error, Overload
LIN Trigger	Condition	Break, ID, ID/Data, Data Error
	Baud Rate	Common, Custom

Waveform

Waveform Measurement

Characteristics	Instruction	
Cursor Measurement	△V, △T, △T&△V between cursors, auto cursor, support XY/FFT/ZOOM window, based on screen percentage	
	Number	2 pairs of XY cursors
	Manual mode	△V, △T
	Tracing mode	The voltage value and time value of the X waveform point are tracked by fixing the Y axis The fixed X-axis tracks the voltage value and time value of the Y waveform point
	Auto measurement cursor	Allows the cursor to be displayed during automatic measurements
	XY Mode	The voltage parameters of the corresponding channel waveforms were measured in XY timebase mode X= Channel 1, Y= Channel 2
Auto measurement	Number	43 automatic measurements with up to 8 measurements displayed simultaneously
	Measurement source	CH1 - CH4
	Measurement area	Primary time base, extended time base, cursor area
	Horizontal	Period, + Width, Rise Time, +Duty, Frequency, - Width, Fall Time, -Duty and ScrDuty
	Vertical	Vavg, Vpp, Vamp, StdDev, Vmax, Vtop, VRMS, Overshoot, Vmin, Vbase, CycRms and Preshoot
	Blend	+PulseCnt, -PulseCnt, RiseCnt, FallCnt, Area and CycArea
	Channel	Delay(1 卐-2 卐), Delay(1 卐-2 卍), Delay(1 卍-2 卐), Delay(1 卍-2 卍), Phase(1 卐-2 卐), Phase(1 卐-2 卍), Phase(1 卍-2 卐), Phase(1 卍-2 卍), FRR(1 卐-2 卐), FRF(1 卐-2 卍), FFR(1 卍-2 卐), FFF(1 卍-2 卍), LRR(1 卐-2 卐), LRF(1 卐-2 卍), LFR(1 卍-2 卐) and LFF(1 卍-2 卍)
Mathematical operation	+, -, * ,/ ,&& ,||, ^, ! (, Tan(, Intg(, Diff(, Sqrt(, Lg(, Ln(, Exp(, Abs(, Sine(, CoSin(, User Defined Function, digital filter (low pass, high pass, band pass, band reject), FFT(Vrms, dBVrms, Radians, Degrees)	

Waveform Analysis

Characteristics	Instruction	
Pass Fail	The signal under test is compared with a user-defined rule (template), providing the number of passes, failures, and the total number of tests. Pass/fail events can trigger immediate stop, buzzer, and screenshot.	
	Source	CH1 - CH4
	Type	Horizontal, vertical and other measurement items
	Measurement	Data statistics: Pass, Fail and the total number
	Acquire mode	All modes are supported except Zoom, XY, FFT and scroll
Color Grade	Provide three view of waveform intensity, color temperature level >16, 256 color scale display	
	Source	CH1 - CH4
	Waveform brightness	brightness
	Acquire mode	Only basic waveforms are supported

Decode

Characteristics	Instruction
Decode Number	2, Both protocol types can be decoded and switched simultaneously
Decode Type	RS232/UART, I2C, SPI, LIN, CAN
RS232/UART	Decode RS232/UART bus TX/RX signals at speeds up to 10 Mb/s (5 to 8 bits), supporting parity bit (odd parity, even parity, or no parity) and stop bit (1 to 2 bits) configuration. Source Channel: CH1~CH4
I2C	Decode the I2C bus addresses (including or excluding the read/write bit), data, and ACK. Source Channel: CH1~CH4
SPI	Decode SPI bus MISO/MOSI data (4 to 32 bits). The mode supports timeout and chip select (CS). Source Channel: CH1~CH4
CAN	Decode remote frames of the CAN bus at speeds up to 1 Mb/s (ID, byte count, CRC), as well as overload frames and data frames (standard/extended ID, control field, data field, CRC, ACK). Supported CAN bus signal types include CAN_H, CAN_L, TX, RX, DIFF. Source Channel: CH1~CH4
LIN	Decode LIN bus versions 1.X or 2.X, with speeds up to 10 kb/s. Decode and display synchronization, identifier, data, and checksum. Source Channel: CH1~CH4

Counter

Characteristics	Instruction
Source	CH1, CH2, CH3, CH4, Follow trigger
Measurement type	Frequency, period
Statistic parameter	Type, Max, Min, Avg
Maximum frequency	Maximum analog bandwidth
Resolution	6 bits

DVM

Characteristics	Instruction
Source	CH1, CH2, CH3, CH4
Function	AC RMS, DC, AC+DC RMS
Resolution	4 bits
Limit warnings	Support upper and lower limit setting, over-limit condition setting, over-limit prompt

Command

Characteristics	Instruction
Common support	Supports the standard SCPI command set
Error message Definition	Error Message
Support status reporting mechanism	Status Reporting
Support for synchronization mechanisms	Synchronization

General Technical Specification

Display

Characteristics	Instruction
Display Type	10.1 inch Colored LCD (Liquid Crystal Display)
Display Resolution	1024 (Horizontal) × 600 (Vertical) Pixels
Display Colors	24 colors, TFT
Grid	18 horizontal cells * 10 vertical cells
Afterglow	Off, infinity, adjustable time (1 second, 2 seconds, 5 seconds)
Brightness level	256 levels

Processor system

Characteristics	Instruction
System memory	2GB RAM
Operating system	Android
Internal non-volatile memory	8GB

Output of the Probe Compensator

Characteristics	Instruction
Output voltage(typical)	About 3.3 V, with the Peak-to-Peak voltage ≥1MΩ
Frequency(typical)	1 kHz Square

Others

Characteristics	Instruction
Communication Interface	HDMI; USB device *1, USB Host *1 ; Trig Out(P/F); LAN interface
Power Supply	AC Input: 100 - 240 V/AC, 50 / 60 Hz, 55 W max.; CAT II DC Input: 15 V/DC 3 A (via USB-C®)
Power Consumption	55W max.
Fuse	2A, T Level, 250 V
Touch Screen	Multi-touch Capacitive screen

Description:
[1] The adapter or battery should support the 15V handshake protocol, with a power requirement of 45W.

Environment

Characteristics	Instruction
Temperature	Working temperature: 0℃ ~ 40℃ Storage temperature: -20℃ ~ +60℃
Relative humanity	≤90%
Height	Operating: 3,000 m Non-operating: 15,000 m
Cooling Method	Fan cooling

Mechanical Specifications

Characteristics	Instruction
Dimension	325mm x 111.5mm x 209mm(L*W*H)
Weight	Approx. 3.2kg

Interval Period of Adjustment:

One year is recommended for the calibration interval period.

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.
Copyright 2026 by Conrad Electronic SE. *3451429_V1_0126_02_ds