



POWER ADAPTER W65ACC GaN

Fast Charger

Technical Information

Colour:	black, white
Surface:	plastic
Input connector:	EU connector
Input voltage:	100 - 240 V
Input alternating current frequency:	50 / 60 Hz
Connections:	USB-C 1, USB-C 2, USB-A
Output, max*:	supports (downwards compatible) PD 3.0, PPS und QC 4.0 USB-C 1/2: max. 65.0 W PPS: 3.3 – 11.0 V/DC 5.0 A, max. 55.0 W USB-A: max. 60.0 W
Average efficiency:	91.43 %
Efficiency at low load (10 %):	84.46 %
Power consumption at no load:	0.26 W
Dimensions:	44.4 x 29.4 x 91.22 mm
Weight:	143.4 g
VPE:	2 pcs

Product Data

Colour	Article no	EAN
black	7806510	4 034303 035946
white	7806512	4 034303 033379



What is GaN?



GaN adapters are a new type of power adapter that have many advantages compared to conventional silicon-based adapters. GaN stands for Gallium Nitride, a material with a higher power density and efficiency. The use of GaN enables smaller power adapters that can also handle higher voltages and currents and even produce less heat.

This makes our power adapters with **GaN** technology **smaller**, **faster** and above all, more **energy efficient**!

*Detailed information on page 2.

Intenso International GmbH
Gutenbergstraße 2 | 49377 Vechta | Germany

(Intenso)[®]
for everyday life

QUALITY AUDIT
Tested in Germany ✓

www.intenso.eu



POWER ADAPTER W65ACC GaN

Fast Charger

Output in detail

Output:	supports (downwards compatible) PD 3.0, PPS und QC 4.0 USB-C 1/2: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 15.0 V/DC 3.0 A, max. 45.0 W 20.0 V/DC 3.25 A, max. 65.0 W PPS: 3.3 – 11.0 V/DC 5.0 A, max. 55.0 W USB-A: 4.5 V/DC 5.0 A, max. 22.5 W 5.0 V/DC 4.5 A, max. 22.5 W 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 20.0 V/DC 3.0 A, max. 60.0 W USB-C 1 + USB-C 2 + USB-A: USB-C 1: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 15.0 V/DC 3.0 A, max. 45.0 W 20.0 V/DC 2.25 A, max. 45.0 W USB-C 2 + USB-A: 5.0 V/DC 3.0 A, max. 15.0 W (shared) Total: max. 60.0 W	USB-C 1 + USB-C 2: USB-C 1: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 15.0 V/DC 3.0 A, max. 45.0 W 20.0 V/DC 2.25 A, max. 45.0 W USB-C 2: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 2.22 A, max. 20.0 W 12.0 V/DC 1.67 A, max. 20.0 W Total: max. 65.0 W USB-C 1 + USB-A: USB-C 1: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 3.0 A, max. 27.0 W 12.0 V/DC 3.0 A, max. 36.0 W 15.0 V/DC 3.0 A, max. 45.0 W 20.0 V/DC 2.25 A, max. 45.0 W USB-A: 5.0 V/DC 3.0 A, max. 15.0 W 9.0 V/DC 2.0 A, max. 18.0 W 12.0 V/DC 1.5 A, max. 18.0 W Total: max. 63.0 W USB-C 2 + USB-A: 5.0 V/DC 3.0 A, max. 15.0 W Total: max. 15.0 W (shared)
---------	---	--