

VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry.

We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.




LI-ION RECHARGEABLE BATTERY USB-C® WITH CHARGING CABLE (USB-A TO USB-C®)

TECHNICAL DATA


Item No.:	3455113	3455114	3455115	3455116
Packaging (pcs per set)	4	4	2	2
Type	Micro AAA HR03	Mignon AA HR6	Baby C HR14	Mono D HR20
Classification	Rechargeable			
Nominal voltage	1.5 V			
Capacity	500 mAh	2000 mAh	2500 mAh	6000 mAh
Heavy metals	Lead(Pb)/Cadmium(Cd)/Mercury(Hg) are not detected(<MDL)			
Lift time expectance	≥ 1200 cycles			
USB-C® input	5 V/DC, 100 mA	5 V/DC, 350 mA	5 V/DC, 500 mA	5 V/DC, 500 mA
Charging time	2 hrs	2.5 - 3 hrs	2.5 - 3 hrs	6 - 7 hrs
Charging status LED	Charging: Green (flashing), Full charge: Green (ON)			
Ambient temperature range	0 to +45 °C charge -20 to +60 °C discharge -20 to +45 °C storage (≤3 months) -20 to +25 °C storage (≤12 months)			

*For performance and safety, observe the operating / storage conditions.

DIMENSIONS AND WEIGHT


BN 3455113											
	<table><tr><td>d1</td><td>10.5 - 0.7 mm</td></tr><tr><td>d2</td><td>3.5 ± 0.5 mm</td></tr><tr><td>h1</td><td>44.5 - 1 mm</td></tr><tr><td>h2</td><td>1.3 ± 0.5 mm</td></tr><tr><td>weight</td><td>approx 7 g</td></tr></table>	d1	10.5 - 0.7 mm	d2	3.5 ± 0.5 mm	h1	44.5 - 1 mm	h2	1.3 ± 0.5 mm	weight	approx 7 g
d1	10.5 - 0.7 mm										
d2	3.5 ± 0.5 mm										
h1	44.5 - 1 mm										
h2	1.3 ± 0.5 mm										
weight	approx 7 g										

BN 3455114




d1	14.3 - 0.5 mm
d2	5.0 - 1mm
h1	50.5 - 1.0 mm
h2	1.5 ± 0.5 mm
Weight:	approx. 19 g

BN 3455115



d1	25.5 - 0.5 mm
d2	max 7.0 mm
h1	50.0 - 2.0 mm
h2	min. 1.5 mm
Weight:	approx. 40 g


BN 3455116




d1	33.0 - 1.0 mm
d2	max 7.0 mm
h1	60.0 - 1.0 mm
h2	min. 2.0 mm
Weight:	approx. 75 ± 5 g

PERFORMANCE CHARACTERISTICS


Standand charge




Low rate discharge



Fast charge



High rate discharge



This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.

*3455113-16_V2_0426_02_dm_ds_en