




With up to 5 switching positions as well as multiple terminal, circuit and slider options, Bulgin's board mounted power slide switches can be configured to suit your needs. We also offer a wide range of voltage selector types that can be either snapped into a panel or flange mounted.

- ⊗ Ratings up to 16A, 250V ac
- ⊗ PCB and solder terminals
- ⊗ Voltage Selector Models
- ⊗ Snap in and flange mounting
- ⊗ 2, 3, 4 and 5 position
- ⊗ Choice of circuits
- ⊗ Choice of actuators



2000 Slide Switches - up to 5 position

10A 250Vac



Key Features

- Slide switches
- Ratings up to 16A, 250V ac
- PCB and solder terminals
- 2, 3, 4 and 5 position
- Choice of circuits
- Choice of actuators

Approvals and specifications

10A 250Vac T85
6(3)A 250Vac T85

UL CSA 16A 250Vac Non Inductive
UL CSA 4A 300Vac
UL 65°C, file no. E45221, CSA file no. LR10990

μ contact gap
Please specify: Standard action (SP116) or Light action (SP118).
2000 series lubrication is inorganic and does not degrade plastics.

Terminal	Series	Position	Circuit	Slider
K 2.8 x 0.8	2	2 Switching positions	10 	0 1 2 3 4 5
R 2.8 x 0.8			20 	
T Solder		3 Switching positions	30 	
X PCB 0.8 Sq.			40 	
Y PCB 0.8 Sq. For mounting stability switches have extra "support" terminals * Nominal - Dimension varies with body type. For exact figure call sales		4 Switching positions	10 	
			20 	
			30 	
			40 	
	5	5 Switching positions	10 	6 7 9 A B C D E G H J K L N P R S T
			20 	
			30 	
			40 	

Examples



X22205C ---



T2220EC ---



T23206A ---
















T24306A ---



T25302A ---




T25100A ---

Body	Options	Dimensions		
C 2 positions  H 2 positions  A 3 positions  H 3 positions  A 4 positions  H 4 positions  A 5 positions 	Colour Call sales for custom colours. A full range is available for large orders. Legend printing A wide range is available For all options call sales	C 2 positions  A 3 positions  A 4 positions  A 5 positions 	H 2 positions  H 3 positions  H 4 positions 	Cut-out /PCB Matrix  for PCB  for PCB  for PCB  for PCB

2000 Slide Switches - Snap fit and panel mount

10A 250Vac



115/230 is preferred legend

Key Features

- 2 way 'voltage selector'
- Ratings up to 16A, 250V ac
- Snap fit and panel mount
- PCB & solder terminals
- 2 and 3 position
- Choice of circuits
- Choice of actuators

Approvals and specifications

10A 250Vac T85
6(3)A 250Vac T85

UL CSA 16A 250Vac Non Inductive
UL CSA 4A 300Vac
UL 65°C, file no. E45221, CSA file no. LR10990

μ contact gap
Please specify: Standard action (SP116) or Light action (SP118).
2000 series lubrication is inorganic and does not degrade plastics.

Terminal	Series	Position	Circuit	Slider
K 2.8 x 0.8	2	2 Switching positions	10 	0 6 C L
R 2.8 x 0.8			20 	
T Solder			30 	
X PCB 0.8 Sq. For mounting stability switches have extra "support" terminals * Nominal - Dimension varies with body type. For exact figure call sales			40 	
	3 Switching positions	3 Switching positions	10 	2 7 D M
			20 	
			30 	
			40 	
	3 Switching positions	3 Switching positions	10 	3 8 E N
			20 	
			30 	
			40 	
	3 Switching positions	3 Switching positions	10 	4 9 H P
			20 	
			30 	
			40 	
	3 Switching positions	3 Switching positions	10 	5 A K R
			20 	
			30 	
			40 	
	3 Switching positions	3 Switching positions	10 	S T
			20 	
			30 	
			40 	

Examples



T22208E ---



T22308E ---



T2230MF ---












T22205B ---



T22305B ---



T23204B ---

Body	Options	Dimensions											
B With mounting holes 	Colour Call sales for custom colours. A full range is available for large orders. Standard body colour is black.	2 Pos B 	3 Pos B 										
E Snap fit 		2 Pos E 	 <table><tr><td>Panel thickness</td><td>Dim. Y</td></tr><tr><td>0.8-1.2</td><td>29.75/29.85</td></tr><tr><td>1.63</td><td>30.15/30.25</td></tr><tr><td>2.0</td><td>30.35/30.45</td></tr><tr><td>2.5</td><td>30.55/30.65</td></tr></table>	Panel thickness	Dim. Y	0.8-1.2	29.75/29.85	1.63	30.15/30.25	2.0	30.35/30.45	2.5	30.55/30.65
Panel thickness		Dim. Y											
0.8-1.2	29.75/29.85												
1.63	30.15/30.25												
2.0	30.35/30.45												
2.5	30.55/30.65												
F Snap fit single contact ON OFF only) 	2 Pos F 	 <table><tr><td>Panel thickness</td><td>Dim. Y</td></tr><tr><td>0.8-1.2</td><td>29.75/29.85</td></tr><tr><td>1.63</td><td>30.15/30.25</td></tr><tr><td>2.0</td><td>30.35/30.45</td></tr><tr><td>2.5</td><td>30.55/30.65</td></tr></table>	Panel thickness	Dim. Y	0.8-1.2	29.75/29.85	1.63	30.15/30.25	2.0	30.35/30.45	2.5	30.55/30.65	
Panel thickness	Dim. Y												
0.8-1.2	29.75/29.85												
1.63	30.15/30.25												
2.0	30.35/30.45												
2.5	30.55/30.65												