

6050 DP Splash Resistant Switches

& Twin Switches - 16A 250Vac



Key Features

- Ratings up to 20A, 277V ac
- Positive switch action
- Distinctive styling
- Illuminated & non-illuminated
- Double Contact
- DC LED Illumination Available
- Panel cut out: 30.1 x 22.2mm






Approvals and specifications

European 16(4)A 250Vac T125, 10A 400Vac T125


UL CSA (except 6054 & 6055 Switches)
20A 277Vac, 250Vac 11/2hp, 125Vac 1hp

UL 100°C, file E45221, CSA file LR10990

3mm contact gap with Positive Break switching.

Terminal	Function	Rocker	Body	Body Colour	
C  6.3 x 0.8	6050  ON - OFF 6051  ON - OFF (momentary ON) 6052  ON - OFF (momentary OFF) 6053  ON - OFF Lit 6054  ON - OFF (momentary ON) Lit 6055  ON - OFF (Single Contact) (momentary ON) Lit 6056  ON - OFF (Single Contact) Isolated light 6057  ON - OFF Isolated light 6058  ON - OFF (Single Contact) Lit 6059  ON - OFF (Single Contact) (momentary ON) Isolated light	6060  ON - ON 6061  ON - ON (momentary 1 side) 6062  2 Circuit ON - ON (In house tests only) 6066  ON - ON (Single Contact) Isolated light 6067  ON - ON Lit 6068  ON - ON 1 Contact ON - OFF Lit 1 Contact 6090  ON - OFF 1 Contact ON - OFF Lit 1 Contact 6091  ON - OFF (momentary ON) Lit 6092  ON - OFF 1 Contact ON - ON 1 Contact Lit Circuits are Double Contact unless described otherwise	A Softline Matt  A Softline Matt  P Lit window Matt  Lit window	L Double Contact Panel cut-out ** Bezel  L Twin units Contact sales for information on splash resistance and IP ratings  P Lit window Matt  Lit window	Lit (DP) A Amber C Clear G Green R Red Un-Lit (DP) B Black R Red W White


Integral Splash Resistance



Current carrying parts are protected from moisture. Droplets which may enter the switch are channelled out through ports in the switch body.

For IP65 see options below

Dimensions



Panel thickness


L 0.75 to 2.5mm


** For cut-out details on momentary switches call sales

Terminal spacing - Contacts 10.5 between centres

Vary with Function

Approvals & ratings vary with function
ON OFF Switches - ON when pressed over terminals 3 & 6.



Rocker Colour	Lamp Voltage	Legend	Legend Colour	Options
B Black	Blank	Blank	Blank	G74 Protective Cover
R Red	2 125V Neon	1223	B Black	Finish Matt is standard.
W White	3 250V Neon		W White	Colour Call sales for custom colours. A full range is available for large orders.
	5 12Vdc LED (P Rocker)			Legend printing Select from the examples or call sales for custom legends.
	6 24Vdc LED (P Rocker)			Protective cover The 6050 series is a water through design. For a higher level of sealing, a snap on cover is available (add G after body code). This reduces panel thickness by 1mm.
	7 12V Filament			
	8 24Vdc Filament			Panel sealing washer W42 is available. This reduces panel thickness by 1.00mm. Covers are not suitable for momentary types.
				IP Ratings Call the sales for details.
				Terminal Link P1067 connects the Contacts of a double Contact switch or twin unit.
				# Mounting orientation may affect IP rating.

Examples



C6050AL - - -



C6053AL - - -



C6053PL - - -



C6000A/C6000AL



C6003P/C6003PL



C6003P/C6030AL