

DATASHEET

M8 60 V Straight coupling, 3-pole, open end, 0.25 mm², black, 10 m

Item No. 3437985

Overview





VIEW A

Pin Assignment		
P1	Wire Color	OPEN
1	Brown	
3	Blue	
4	Black	

TECHNICAL REQUIREMENTS	
Coupling Type	Threaded connection
Tetmination Way	Soldering
Applicable temperature	-40 to +80 ℃
Level of pollution	3
Protection Grade	IP67(Lock)
Durability	≥500
Rated voltage	60V AC/DC
Rated current	3A
Conductor impedance	≤5 mΩ
Insulation impedance	≥ 100 MΩ
Quality standards	IPC-A-620
ELECTRICAL CHARACTERISTICS	
High voltage test	DC 300V / 0.01S
Insulation impedance	10MΩ MIN
Conductor impedance	3Ω MAX
Open short test	100% TEST

3 UL20549 3C*24AWG(7/0.2STC), inner core PVC ,OD:1.1,Jacket black fog surface (GS0827-ZC) 90A TPU polyether flame retardant FT2(coarse and sticky)(3C24-001)

2 M8 overmolding TPU black

1 CAZN M8 female plug semi-finished product 3core:M8-S3A-SFC

Dimensions in mm

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.