

10196000	DATA SHEET	
Valid from: 31.05.2023	EPIC® H-BE 24 SS DR (LP) / H-BE 24 BS DR (LP)	

Description

- Standard inserts with screw termination, crimp termination, cage clamp termination and Push-In termination
- The EPIC® H-BE series is suitable for applications that require a reliable connection when working with high voltages and currents
- Use for railway applications -Brand protection in rail vehicles: test according to EN 45545-2. Requirement sentences R22 and R23. Hazard levels HL1, HL2 and HL3.
- UL tested for control cabinet applications with high SCCR ratings in accordance with UL 508 / UL 2237



General Characteristics

Series	H-BE 24: 1-24; 25-48; 25-48 LP
Version 1-24	Male: 10196000; Female: 10197000
Version 25-48	Male: 10204000; Female: 10205000
Version 25-48 LP	Male: 44423030; Female: 44423029
Wire Protection	Yes
Number of Contacts	24 + PE (48+2xPE)
Termination Methods	Screw termination: 0.5 - 2.5 mm ²
Protection (DIN EN 60529)	IP65
Protection (NEMA 250, UL50E)	12
Temperature Range	-40°C to +100°C, short-term up to +125°C

Mechanical Characteristics

Cycle of mechanical operation	500
-------------------------------	-----

Electrical Characteristics

Rated Voltage, IEC	500 V
Rated Voltage, UL	600 V
Rated Voltage, CSA	600 V
Rated Impulse Voltage	6 kV
Rated Current, IEC	16 A
Rated Current, UL	16 A
Rated Current, CSA	16 A
Contact Resistance	< 2 mOhm
Degree of Soiling	3
SCCR	See PVVA2:E483837

Materials and Surfaces

Contacts	Copper alloy, hard silver-plated
Insulating Body	PC
Flammability Class according to UL 94	V0

Approvals

UL-Approval, E-File-Number	E75770, E483837
VDE-Approval, VDE-REG.-Nr.	B437


Standard

Safety/Application Standard	IEC 61984, UL 1977, CSA22.2 182.3, UL 2237
-----------------------------	--

Creator: THB01/PDP Released: IVSE1/PDP	Document: DB10196000EN Version: 06	Page 1 of 2
---	---------------------------------------	-------------

10196000	DATA SHEET	
Valid from: 31.05.2023	EPIC® H-BE 24 SS DR (LP) / H-BE 24 BS DR (LP)	

Technical Drawings



Robust



Temperature-resistant

Info

Multifunctional insert for versatile applications
Screw, crimp, cage clamp and Push-In version - freely combinable
Also as EPIC® H-BE 48 available

Application range

Mechanical engineering
Light & sound technology
Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

M

F

M


F

13	1
14	2
15	3
16	4
17	5
18	6
19	7
20	8
21	9
22	10
23	11
24	12

1	13
2	14
3	15
4	16
5	17
6	18
7	19
8	20
9	21
10	22
11	23
12	24

37	25
38	26
39	27
40	28
41	29
42	30
43	31
44	32
45	33
46	34
47	35
48	36

25	37
26	38
27	39
28	40
29	41
30	42
31	43
32	44
33	45
34	46
35	47
36	48



EPIC H-BE 24 SS DR 25-48 LP



EPIC H-BE 24 BS DR 25-48 LP

Creator: THB01/PDP Released: IVSE1/PDP	Document: DB10196000EN Version: 06	Page 2 of 2
---	---------------------------------------	-------------