

19135000	DATA SHEET	
Valid from: 29.08.2022	EPIC® H-B 32 TS	

Description

- The large, robust housing for two inserts of size 16



General Characteristics

Series	H-B 32
Version	Hood
Locking	Bolts for double lever
Cable entry	1x lateral, see table
Gland body	See table
Protection (DIN EN 60529)	IP 65 (latched)
Temperature Range	-40°C to +100°C, short term up to +125°C

Materials / Surfaces

Housing	Aluminium alloy, powder-coated, grey
Locking	Steel, zinc-plated
Gland body	Brass, nickel-plated

Standard

Safety Standard	IEC 61984
-----------------	-----------


Versions

Article number	Article description	Cable entry	Gland body
10135000	EPIC® H-B 32 TS 21 ZW	Pg 21	Yes
10135600	EPIC® H-B 32 TS 29	Pg 29	No
10136000	EPIC® H-B 32 TS 29 ZW	Pg 29	Yes
19135000	EPIC® H-B 32 TS M25	M25	No
19136000	EPIC® H-B 32 TS M32	M32	No
19136200	EPIC® H-B 32 TS M40	M40	No

Creator: BEGE1/PDP Released: IVSE1/PDP	Document: DB19135000EN Version: 00	Page 1 of 2
---	---------------------------------------	-------------

19135000	DATA SHEET	
Valid from: 29.08.2022	EPIC® H-B 32 TS	

Technical Drawings



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Application range

Plant engineering, Control engineering, Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: BEGE1/PDP Released: IVSE1/PDP	Document: DB19135000EN Version: 00	Page 2 of 2
---	---------------------------------------	-------------