

61742400	DATA SHEET
Valid from: 14.03.2024	Shrink tube PROTECT

Shrink tube for industrial applications:
For electrical insulation, Strain relief, wire bundling and protection.



Material: Polyolefin


Technical features:

Shrink ratio 2:1
Shrink temperature >90°C
Temperature range -55°C bis +135°C

Color: black
green/yellow

Additional features:

Tensile strength 13 N/mm²
Elongation at break 300%
Longitudinal change -10% up to +1%
Dielectric strength 20 kV/mm
Volume resistivity 10¹⁴ Ω/cm
Flammability acc. to UL 224



Dimensions:

Package Unit	Part No.	Size D inch	Inner Diameter mm		Recovered wall thickness w mm
			supplied D	recovered d	
Box					
	Black				
	61742423	3/64	1,2	0,6	0,41
	61742424	1/16	1,6	0,8	0,43
	61742425	3/32	2,4	1,2	0,51
	61742426	1/8	3,2	1,6	0,51
	61742427	3/16	4,8	2,4	0,51
	61742428	1/4	6,4	3,2	0,65
	61742429	3/8	9,5	4,8	0,65
	61742430	1/2	12,7	6,4	0,65
	61742431	3/4	19,1	9,5	0,77
	61742433	1	25,4	12,7	0,89
Pieces					
	Black				
	61742400	3/64	1,2	0,6	0,41
	61742401	1/16	1,6	0,8	0,43
	61742402	3/32	2,4	1,2	0,51

61742400	DATA SHEET
Valid from: 14.03.2024	Shrink tube PROTECT

	61742403	1/8	3,2	1,6	0,51
	61742404	3/16	4,8	2,4	0,51
	61742405	1/4	6,4	3,2	0,65
	61742406	3/8	9,5	4,8	0,65
	61742407	1/2	12,7	6,4	0,65
	61742408	3/4	19,1	9,5	0,77
	61742409	1	25,4	12,7	0,89
	Green/Yellow				
	61742416	1/8	3,2	1,6	0,51
	61742417	3/16	4,8	2,4	0,51
	61742418	1/4	6,4	3,2	0,65
	61742419	3/8	9,5	4,8	0,65
	61742420	1/2	12,7	6,4	0,65
	61742421	3/4	19,1	9,5	0,77
	61742422	1	25,4	12,7	0,89

Commodity product, not a Lapp product.