



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED, AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED, ARE BEYOND PANDUIT'S CONTROL.



TEAR-TAB



ADHESIVE BACKING: PRESSURE SENSITIVE FOAM TAPE, .04(1.0) THICK, WITH RUBBER (-A) ACRYLIC (-AT) OR HIGH BOND ACRYLIC (-AV) ADHESIVE AND PROTECTIVE LINER. LINER TO EXTEND BEYOND EDGE TO FORM TEAR-TAB. MOUNT IS DESIGNED TO SUPPORT .20 lbs. (91g) MAX. WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE.


PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in. (mm)	WEIGHT lbs. (g) / 100pcs
ACC19-A	.19 (4.8)	.17 (77)
ACC19-AT	.19 (4.8)	.17 (77)
ACC19-AV	.19 (4.8)	.17 (77)

TO APPLY ADHESIVE CORD CLIP:

1. REMOVE PROTECTIVE LINER
2. PLACE IN DESIRED LOCATION
3. APPLY PRESSURE TO TOP OF CORD CLIP

NOTES:

- * 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

							TITLE ADHESIVE CORD CLIP ACC19-A , ACC19-AT , ACC19-AV CUSTOMER DRAWING					
01C 2/26/15 RVU CLW JHAC SHOW THE TEAR TABS IN THE CORRECT LOCATION. GAECN02632							ITEM REVISION NAME G03597BC/01					
00B 11/6/09 TMSA ADDED PART NUMBER ACC19-AV. REVISED TO TEAMCENTER NAMING CONVENTION. GB0239GG							DATASET FILE NAME G03597BC_DC_GB0239GG/01C					
2 6/5/03 MSAD MODIFIED BASE LENGTH AND WIDTH DIMENSIONS. GB0239GG							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± N/A .xxx ± N/A .xx ± .02 [.5] ANGLES ± 5 ° 		MATERIAL: NYLON 6/6			
1 7/15/99 CGSM REPLACED ISO VIEW GB0239GG												
R 2/23/99 CGSM RE-DRAWN FROM DWG SS-7173 GB0239GG							THIRD ANGLE PROJECTION		DRAWING NUMBER: GB0239GG			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY CGSM	DATE 2/23/99	CHK JHAC	SCALE FULL	SHT 1 OF 1	SIZE A