



Technical drawing of the front view of a 1/2 inch x 1/2 inch x 1/2 inch angle. The drawing shows a cross-section of the angle with a rounded top. Dimensions are provided for the top radius, the width of the flat base, and the total width of the angle. The top radius is 0.610 inches (15.5 mm). The width of the flat base is 0.97 inches (24.6 mm). The total width of the angle is 1.01 inches (25.7 mm).



1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

2. PART IS DESIGNED TO SUPPORT MAXIMUM WEIGHT ON A CLEAN, DRY, SMOOTH SURFACE. SEE TABLE.



NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

FORM 040 (11-07) PANDUIT'S CONFIDENTIAL WITH PROTECTIVE LINER.										DIMENSIONS IN BRACKETS ARE METRIC [mm]									
										CAD FILENAME/LAYERS GB0430BA_PB_LC5-A_02									
																			
										LATCHING CLIP (LC5-A)									
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ± 5°					UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.				
2	6-29-01	LGG		ADDED REF & UPDATED	GB0430BA	2				DRAWN BY	SJSU	MAT'L: RIGID PVC	SCALE NONE						
1	2-16-94	SJSU		REVERSED TEAR TAB	GB0430BA	1				DATE	12/3/93		DRAWING NO. GB0430BA						
R	12/3/93	SJSU		INITIAL RELEASE	GB0430BA	R				CHK'D			DWG A SIZE						
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP											