



Read this document carefully before using this device. The guarantee will be expired by device damages if you don't attend to the directions in the user manual. Also we don't accept any compensations for personal injury, material damage or capital disadvantages.

ENDA ET2411 ON/OFF HEAT CONTROLLER

Thank you for choosing **ENDA ET2411 ON/OFF Heat Controller**.

- ▶ 77 x 35mm sized.
- ▶ Single NTC sensor input.
- ▶ Zero point input shift.
- ▶ Selectable heating or cooling control for C1 relay output.
- ▶ Selectable heating or cooling control.
- ▶ In the case of sensor failure, relay state can be set to ON or OFF.
- ▶ Upper and lower setpoint limits can be adjusted.
- ▶ Temperature unit can be selected as °C or °F.
- ▶ CE marked according to European Norms.




Order Code : ET2411 - 1 - Supply Voltage
230.....230V AC
LV.....10-30V DC /
8-24V AC



ENDA ET2411 is intended for installation within control panels. Make sure that the device is used only for intended purpose. The shielding must be grounded on the instrument side. During an installation, all of the cables that are connected to the device must be free of electrical power. The device must be protected against inadmissible humidity, vibrations, severe soiling. Make sure that the operation temperature is not exceeded.

All input and output lines that are not connected to the supply network must be laid out as shielded and twisted cables. These cables should not be close to the power cables or components. The installation and electrical connections must be carried out by a qualified staff and must be according to the relevant locally applicable regulations.



Equipment is protected throughout by **DOUBLE INSULATION**

Holding screw **0.4-0.5Nm.**

NOTE:

SUPPLY:
184-253V AC
or
10-30V DC /
8-24V AC
50/60Hz 5VA

Line 5
Neutral 6

Fuse F 100 mA
250V AC

Switch

230V AC or LV
Supply

Fuse should be connected

Cable size: 1,5mm²

Note:

- 1) Mains supply cords shall meet the requirements of IEC 60227 or IEC 60245.
- 2) In accordance with the safety regulations, the power supply switch shall bring the identification of the relevant instrument and it should be easily accessible by the operator.

TECHNICAL SPECIFICATIONS

INPUT		
Input Type	Scale Range	Accuracy
NTC Sensor Typ 103AT-2 at 25 °C - 10 kOhm	EN 60751 -60.0...150.0 °C -76.0...302.0°F	± 1% (for full scale) ± 1 Digit
ENVIRONMENTAL CONDITIONS		
Ambient/Storage temperature	0 ... +50 / °C -25... +70°C(without icing)	
Relative Humidity	Max. humidity 80% for temperatures up to 31°C decreasing linearly to 50% relative humidity at 40°C.	
Protection Class	According to EN60529; Front panel: IP65 Rear panel : IP20	
Height	Max. 2000m	
	Do not use the device in locations subject to corrosive and flammable gasses.	
ELECTRICAL CHARACTERISTICS		
Supply	230V AC +10% -20% 50/60Hz ; 10-30V DC / 8-24V AC SMPS	
Power Consumption	Max. 3VA	
Wiring	Power connector : 2.5mm² screw-terminal, Signal connector : 1,5mm² screw-terminal conenction.	
Line Resistance	Max. 100ohm	
Data Retention	EEPROM (Min. 10 years)	
EMC	EN 61326-1 : 2013 (Performance criterion B is satisfied for EN 61000-4-3)	
Safety Requirements	EN 61010-1 : 2010 (Pollution degree 2, overvoltage category II)	
Indicator	4 digits, 12.5mm, 7 segment red LED	
OUTPUT		
C1 Output	For 8A Models : 250V AC, 8A (resistive load), NO and NC control output.	

Life Expectancy for Relay For 8A Models : 30. Mio. Switching for no-load operation; 300.000 switching for 8A resistive load at 250VAC.

CONTROL


Control Type	Single-setpoint and alarm control.
Control Algorithm	On-Off Control.
A/D Converter	12 bit resolution, 100ms sampling time.
Hysteresis	Adjustable between 0.1 and 20.0°C/F.

HOUSING

Housing Type	Suitable for flush-panel mounting according to DIN 43 700.
Dimensions	W77xH35xD61mm
Weight	Approx. 215g (After packing)
Enclosure Materials	Self extinguishing plastics

While cleaning the device, solvents (thinner, benzine, acid etc.) or corrosive materials must not be used.

Dimensions



Programming Diagram

