

## 5 pcs ESD Brush Set Part-No.: 25EC170



|         | Length(cm) | Hairs Surface(cm) | Length of Hairs(cm) | Color |
|---------|------------|-------------------|---------------------|-------|
| Brush 1 | 17.0       | 6.1 x 0.8         | 2.5                 | Black |
| Brush 2 | 14.3       | 4.7 x 0.8         | 2.5                 | Black |
| Brush 3 | 14.1       | 3.8 x 0.8         | 2.5                 | Black |
| Brush 4 | 14.8       | 1.8 x 0.8         | 1.8                 | Black |
| Brush 5 | 12.0       | Φ1.1              | 1.6                 | Black |

### Characteristics:

Allow through cleaning of ESD sensitive assemblies without the danger of high charges generated by conventional brushes.

Handle: made of Conductive carbon loaded polypropylene.

Surface Resistance:  $<10^5 \Omega$

Bristle Head: bristles made of polyamide.

Hair: Black colour, ~0.4 mm in diameter

Application: Clearing PCB, Surface of the Electronic Products.

## 5pcs ESD Plastic Tweezers Set Part-No.: 25EC170



| Type                          | Length (mm) | Weight(g) | Gap Between Tips while Open(mm) |
|-------------------------------|-------------|-----------|---------------------------------|
| Straight Round Tips, 2mm wide | 115         | 5         | 6.5                             |
| Straight Flat Tips, 6mm wide  | 115         | 4         | 12                              |
| Straight Flat Tips, 3mm wide  | 115         | 5         | 7                               |
| Bent pointed Tips             | 115         | 5         | 5                               |
| Straight pointed tips         | 115         | 4         | 6.5                             |

### Specifications:

Material: Conductive, Black Plastic

Electrostatic Dissipative, protects electronic components from static damage during precise operation

Anti-magnetic, Resistant to most Acids and other Corrosives.