

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry.

We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

LI-ION RECHARGEABLE BATTERY WITHOUT BMS




TECHNICAL DATA


Item No.:	3533196	3533198	3533199	3533200	3533201	3533202	3533211
Type (Cylindrical)	18650	18650	18650	21700	18350	26650	14500
Classification	Rechargeable						
Chemical system	Lithium-ion						
Nominal voltage	3.6 V	3.6 V	3.6 V	3.7 V	3.7 V	3.7 V	3.7 V
Capacity	2550 mAh	3000 mAh	3350 mAh	5000 mAh	1100 mAh	5000 mAh	1000 mAh
Charging current	1250 mA typ 2500 mA max.	1500 mA typ 6000 mA max	1625 mA typ 3250 mA max	2500 mA typ 5000 mA max	200 mA typ 1200 mA max	1000 mA typ 2500 mA max	200mA typ 1200mA max
Discharge current	500 mA typ 7500 mA max	600 mA typ 10000 mA max	650 mA typ 9750 mA max	1000 mA typ 15000 mA max	200 mA typ 3000 mA max	1000 mA typ 5000 mA max	200mA typ 3000mA max
Operating conditions	-20 to +60 °C						
Storage conditions	-20 to +45 °C						
Compliance	IEC 62133-2						

PERFORMANCE CHARACTERISTICS


Standard charge




Fast charge



Low rate discharge



High rate discharge



DIMENSIONS

Item No.: 3533196  d1 max. 18.8 mm h1 max. 70.0 mm	Item No.: 3533198  d1 max. 18.8 mm h1 max. 70.0 mm	Item No.: 3533196  d1 max. 18.8 mm h1 max. 70.0 mm
Item No.: 3533200  d max. 21.4 mm h max. 70.8 mm	Item No.: 3533201  d1 max. 18.5 mm h1 max. 34.8 mm	Item No.: 3533202  d1 max. 26.2 mm h1 max. 65.5 mm
Item No.: 3533211  d1 max. 14.0 mm h1 max. 49.4 mm	