

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

KT-100 LAN CABLE TESTER



Item no. 3474774

FEATURES

// Max. testable cable length: 305 m // Multifunction cable tester - supports phone (RJ11/RJ12), network (RJ45), and coaxial cables (F-connector) cables // Backlit LCD display // Identifies wiring errors: split pair, shorts, open wires, miswired, and reverse pairs // 3 tone patterns: by pin, by pair, all pins //

TECHNICAL DATA

Power supply.....1x 9 V battery
Voltage between any
two pins without damage (max.)....60 V/DC or 55 V/AC
Cable types..... Shielded or unshielded:
Cat 7, Cat 7a, Cat 6a, Cat 6,
Cat 5e, Cat 5, Cat 3
Cable length (max.).....305 m
Cable length for splitpair
detection (min.).....0.5 m
Cable resistance (max.).....100 Ω max. DC
Operating conditions.....0 to +50 °C, 10 – 90 % RH (non-condensing)
Storage conditions.....-20 to +60 °C, 10 – 90 % RH (non-condensing)
Dimensions (W x H x D).....70 x 181 x 38 mm
Weight.....approx. 226 g (without battery)

PACKAGE CONTENTS

- LAN cable tester
- 1x 9V Battery
- 2x RJ45 to RJ45 connector cable
- 2x RJ12 to RJ12 connector cable
- 1x F-to-F coaxial cable adapter cable
- 5x RJ45 Remote
(5 numbered Remote ID's permit mapping 5 remote locations)
- 5x F-Connector Remote
(5 numbered Remote ID's permit mapping 5 remote locations)
- 1x Canvas carrying case

