

VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

VC-55 S TWO-POLE VOLTAGE TESTER

CE

Item no. 3558033

The two-pole voltage tester is built and tested according to EN 61243-3/VDE0682. The voltage display occurs through bright LEDs that are distributed in ranges from 12 - 690 V and also as real effective value from 0 - 690 V in the LCD display.

FEATURES

CAT III 1000 V, CAT IV 600 V // LED and LCD display // Continuity test // One-pole phase testing // Rotary field testing // Integrated LED measuring point illumination //

TECHNICAL DATA

Display	LED/LCD
Measurement range for voltage (LED)	0 - 690 V AC/DC
Frequency range	DC, 16 - 400 Hz
Interior resistance	200 kOhm
Max. test current	3.5 mA
One-pole phase testing	90 - 690 V/AC
Measurement category	CAT III 1000 V, CAT IV 600 V
Operating condition	-15 to +55 °C,
Storage condition	-20 to +70 °C,
Protection type	IP64
Power supply	Micro batteries (AAA) 1.5 V x 2
Cable length	1.2 m
Dimensions (H x W x D)	258 x 65 x 25 mm
Weight (approx.)	185 g (Not include battery)



EQUIPMENT:

Direct and alternating current testing (LED/LCD) // Polarity test (LED/LCD) // Optical continuity test // Screw-on 4 mm probe adapters for permitted contacting of socket contacts // Attachable hand grip for one-handed operation.

PACKAGE CONTENTS:

VC-55 S LCD // 2 probe adapters 4 mm // 2 push-on caps // Probe cover // Batteries
// Operating instructions.