


DATASHEET


Shock Absorbers

Item No.	Model No.	Thread	Stroke (mm)	Max. Energy/cycle (Nm)	Max. Energy/Hour (Nm/hr)	Max. Effective Mass (kg)	Max. Impact Speed (m/s)	Operating Temp. (°C)
3582714	TC-AC0604-2	M6x0.75	4	1.8	6480	1.8	1	-10 to +85
3582715	TC-AC0806-2	M8x1.0	6	2	7200	2	1	-10 to +85
3582716	TC-AC1005-2	M10x1.0	5	3	10800	3	1.5	-10 to +85
3582717	TC-AC1008-2	M10x1.0	8	4	14400	4	1.5	-10 to +85
3582718	TC-AC1210-2	M12x1.0	10	5	18000	10	1.5	-10 to +85
3582719	TC-AC1412-2	M14x1.5	12	15	36000	50	1.5	-10 to +85
3582720	TC-AC1416-2	M14x1.5	16	20	40000	70	1.5	-10 to +85
3582721	TC-AC2020-2	M20x1.5	20	40	48000	200	2	-10 to +85
3582722	TC-AC2030-2	M20x1.5	30	50	54000	200	2	-10 to +85
3582723	TC-AC2525-2	M25x1.5	25	80	60000	600	2.5	-10 to +85
Note: All models feature self-compensation technology.								

Item No.: 3582714



Item No.: 3582715




units: mm




DATASHEET


Item No.: 3582716




Item No.: 3582717



Item No.: 3582718




Item No.: 3582719




units: mm

DATASHEET


Item No.: 3582720




Item No.: 3582721



Item No.: 3582722



Item No.: 3582723



units: mm