

00009371	DATA SHEET	
Valid from: 23.05.2022	EPIC® SIGNAL R 3.0 G1	

Description

- Circular connectors with solder termination
- 21-pin and 26-pin
- highest contact density at small space requirements
- Connector in solder version for easy maintenance



General Characteristics

Series	SIGNAL R 3.0 G1
Number of contacts	21-pin / 26-pin
Pin configuration	Male E-part / Female P-part
Coding	N
Rated voltage (V)	24V AC / 60VDC
Rated impulse voltage	1,5 kV
Rated current (A)	7,5 A
Contact resistance	< 3 mOhm
Contacts	Copper alloy, gold plated
Termination methods	Solder termination: up to 1.0 mm²
Fastening type	Ø25mm (1x)
Protection	IP 67 (maximum, dependant on cable gland used)
Cycle of mechanical operation	500
Temperature range	-40°C to +100°C, short-term up to +125°C

Materials and Surfaces

Housing	Nickel plated copper alloy
Insert	Thermoplastic
Sealing	Chloroprene Rubber

Versions


Article number	Article description	Version	Contacts	Pin configuration	Fastening type	Coding
00009371	EPIC® SIGNAL R 3.0 G1	male	1 - 21	E-Part	Ø25mm (1x)	N
00009894	EPIC® SIGNAL R 3.0 G1	male	1 - 26	E-Part	Ø25mm (1x)	N
00009057	EPIC® SIGNAL R 3.0 G1	female	1 - 21	P-Part	Ø25mm (1x)	N
00009005	EPIC® SIGNAL R 3.0 G1	female	1 - 26	P-Part	Ø25mm (1x)	N

Creator: FICE1/PDP Released: VACH1/PDP	Document: DB00009371EN Version: 02	Page 1 of 3
---	---------------------------------------	-------------

00009371	DATA SHEET	
Valid from: 23.05.2022	EPIC® SIGNAL R 3.0 G1	


Technical Drawings

Housing




Inserts (plug-side view)


00009057
P-Part / female 21 pins




00009371
E-Part / male 21 pins



00009005
P-Part / female 26 pins



00009894
E-Part / male 26 pins



Creator: FICE1/PDP Released: VACH1/PDP	Document: DB00009371EN Version: 02	Page 2 of 3
---	---------------------------------------	-------------

00009371	DATA SHEET	
Valid from: 23.05.2022	EPIC® SIGNAL R 3.0 G1	



Corrosion-resistant



Industrial machinery and plant engineering



Mechanical resistance



Space requirement

Application range

Machine and equipment manufacturing

Measurement and control technology

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: FICE1/PDP Released: VACH1/PDP	Document: DB00009371EN Version: 02	Page 3 of 3
---	---------------------------------------	-------------