

|                           |                        |                                                                                     |
|---------------------------|------------------------|-------------------------------------------------------------------------------------|
| 19474000                  | <b>DATA SHEET</b>      |  |
| Valid from:<br>29.08.2022 | <b>EPIC® H-A 32 SG</b> |                                                                                     |

## Description

- The large, robust housing for two inserts of size 16.



## General Characteristics

|                           |                                          |
|---------------------------|------------------------------------------|
| Series                    | H-A 32                                   |
| Version                   | Surface-mount base                       |
| Locking                   | Double lever                             |
| Cable entry               | Lateral, see table                       |
| Gland body                | See table                                |
| Protection (DIN EN 60529) | IP 65 (latched)                          |
| Temperature Range         | -40°C to +100°C, short term up to +125°C |

## Materials / Surfaces

|            |                                      |
|------------|--------------------------------------|
| Housing    | Aluminium alloy, powder-coated, grey |
| Locking    | Steel, zinc-plated                   |
| Gland body | Brass, nickel-plated                 |
| Sealing    | NBR                                  |

## Standard

|                 |           |
|-----------------|-----------|
| Safety Standard | IEC 61984 |
|-----------------|-----------|


## Versions

| Article number | Article description      | Cable entry<br>(right) | Cable entry<br>(left) | Gland body |
|----------------|--------------------------|------------------------|-----------------------|------------|
| 10474000       | EPIC® H-A 32 SGR 21 ZW   | Pg 21                  | -                     | Yes        |
| 10474100       | EPIC® H-A 32 SGR 29 ZW   | Pg 29                  | -                     | Yes        |
| 10482000       | EPIC® H-A 32 SGRL 21 ZW  | Pg 21                  | Pg 21                 | Yes        |
| 19474000       | EPIC® H-A 32 SGR M25 ZW  | M25                    | -                     | Yes        |
| 19474100       | EPIC® H-A 32 SGR M32 ZW  | M32                    | -                     | Yes        |
| 19482000       | EPIC® H-A 32 SGRL M25 ZW | M25                    | M25                   | Yes        |
| 19482100       | EPIC® H-A 32 SGRL M32 ZW | M32                    | M32                   | Yes        |
| 79506800       | EPIC® H-A 32 SGRL M40    | M40                    | M40                   | No         |

|                                           |                                       |             |
|-------------------------------------------|---------------------------------------|-------------|
| Creator: BEGE1/PDP<br>Released: IVSE1/PDP | Document: DB19474000EN<br>Version: 00 | Page 1 of 2 |
|-------------------------------------------|---------------------------------------|-------------|

|                           |                        |                                                                                     |
|---------------------------|------------------------|-------------------------------------------------------------------------------------|
| 19474000                  | <b>DATA SHEET</b>      |  |
| Valid from:<br>29.08.2022 | <b>EPIC® H-A 32 SG</b> |                                                                                     |

## Technical Drawings



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

## Application range

Machine and equipment manufacturing, Control engineering

## Remark

Photographs are not to scale and do not represent detailed images of the respective products.

|                                           |                                       |             |
|-------------------------------------------|---------------------------------------|-------------|
| Creator: BEGE1/PDP<br>Released: IVSE1/PDP | Document: DB19474000EN<br>Version: 00 | Page 2 of 2 |
|-------------------------------------------|---------------------------------------|-------------|