

DATASHEET

Quick Straight Joint

Technical data

Item No.	Model No.	E	A	B	C	D	F	Weight (g)
3594587	TC-BKC0425-G01	G1/8	18.5	8	12	5.5	Ø 4	7.7
3594588	TC-BKC0425-G02	G1/4	22.3	8	12	7	Ø 4	11.26
3594589	TC-BKC0640-G01	G1/8	21	10	12	5.5	Ø 6	10.73
3594590	TC-BKC0640-G02	G1/4	25	10	10	7	Ø 6	14.28
3594591	TC-BKC0850-G01	G1/8	22	13	12	5.5	Ø 8	14.64
3594592	TC-BKC0850-G02	G1/4	26	13	12	7	Ø 8	19.33
3594593	TC-BKC1065-G02	G1/4	28.5	15	16	7	Ø 10	32.91
3594594	TC-BKC1065-G03	G3/8	28.5	15	21	7	Ø 10	37.58
3594595	TC-BKC1280-G03	G3/8	28	17	21	7	Ø 12	35.41
3594596	TC-BKC1280-G04	G1/2	29.5	17	21	8.5	Ø 12	41.22

Measurements for A, B, C, D, F in mm // E is non-metric

Others

Material.....Brass










Coating.....Nickel

Suitable medium.....Clean compressed air

Pressure range.....0.1 - 1.6 Mpa

Operating temperature-20 to +80 °C



Item no.: 3594587 	Item no.: 3594588 
Item no.: 3594589 	Item no.: 3594590 
Item no.: 3594591 	Item no.: 3594592 
Item no.: 3594593 	Item no.: 3594594 
Item no.: 3594595 	Item no.: 3594596 