

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry.

We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

NiMH RECHARGEABLE BATTERY 9V



TECHNICAL DATA


Item No.:	3533192	3533193	3455106
Packaging (pcs/set)	1	1	4
Type	NiMH (9V)		
Classification	Rechargeable		
Terminal type	Block 6LR61		
Nominal voltage	8.4 V		
Capacity	200 mAh	270 mAh	270 mAh
Heavy metals	Lead(Pb)/Cadmium(Cd)/Mercury(Hg) are not detected(<MDL)		
Standard charge (14-16 hrs)	20 mA	27 mA	27 mA
Fast charge	200 mA (1.2 hrs)	270 mA (1.1 hrs)	270 mA (1.1 hrs)

Ambient temperature range

- 0 to +45 °C standard charge
- 10 to +40 °C fast charge
- 20 to +65 °C discharge (≤ 1.0 °C)
- 0 to +45 °C discharge (> 1.0 °C)
- 20 to +50 °C storage (≤ 3 month)
- 20 to +40 °C storage (≤ 6 months)
- 20 to +30 °C storage (≤ 24 months)


*For performance and safety, observe the operating / storage conditions.

DIMENSIONS AND WEIGHT




PERFORMANCE CHARACTERISTICS


Standard charge




Fast charge



Low rate discharge



High rate discharge



This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE. *3533192_93_3455106_V1_0326_02_dm_ds_en