

**PRODUCT
DATASHEET**



SMFF1206P2000~3000 Surface Mount Fuses Devices

SMFF1206P2000~3000 Surface Mount Fuses Devices

Description

Polytronics SMFF1206 series surface mount fast-acting fuse utilizes thick film process with extremely stable fusing element. The glass over coating can tolerate higher temperature profile, and the non-flammable ceramic substrate offers better heat conductivity and safety. SMFF1206 series is also RoHS compliant and halogen-free to meet global environmental standard.

Features

- Fast acting
- Compact size
- Thick film manufacturing method
- Ceramic substrate with silver fusing element
- Excellent environmental integrity



Application

- Battery pack
- PC related equipment / peripherals
- Digital camera
- Power supply
- Game equipment
- Wireless base station
- LCD monitor, LCD modules
- Medical device

Agency Approval and Environmental Compliance

Agency	File Number	Regulation	Standard
	UL/CSA:E331807		2011/65/EU
			IEC 61249-2-21:2003

Electrical Characteristics

Part Number	Marking	Current Rating (A)	Voltage Rating	Interrupting Rating	Typical Cold DCR† (Ω)	Typical I²T‡ (A²S)	Agency Approval
SMFF1206P2000	20	20.0	48V DC	300A / 32V DC 200A / 48V DC	0.0017	48	
SMFF1206P2500	25	25.0			0.0013	70	✓
SMFF1206P3000	30	30.0			0.0010	90	✓

† Measured at ≤10% rated current and 25°C

‡ Melting I²T at 10 times of rated current

SMFF1206P2000~3000 Surface Mount Fuses Devices

Electrical Specification

Ampere Rating	% of Current Rating	Opening Time
20.0A~30.0A	100%	4 Hours Min.
	350%	5 Seconds Max.


Physical Specifications

Materials	Substrate: Ceramic Terminations: Silver over-plated with tin (100%) Element: Silver or Silver/Palladium
Solderability	MIL-STD-202
Soldering Parameters	Wave Solder: 260°C, 10 seconds max. Reflow Solder: 260°C, 5 seconds max. Hand Solder: 350°C, 5 seconds max.

Environmental Specifications


Operating Temperature	-55°C to 125 °C
------------------------------	-----------------

Thermal Derating Curve




SMFF1206P2000~3000 Surface Mount Fuses Devices

Time-Current Curve



I²T vs Time Curve



Physical Dimensions (mm.)

Dimensions (mm)


L	W	T	D
3.10±0.20	1.55±0.20	0.80±0.20	0.65±0.20

Recommended Solder Pad Dimension (mm)

A	B	C	D
4.4±0.5	2.4±0.3	1.2±0.3	2.0±0.3


Dimensions of Standard Test Board (mm)

Ampere Rating	Board Thickness	Copper Layer Thickness	Copper Trace Width
20A~30A	1.6	0.175	10.0



Part Number

SMF F 1206 P □□□□



SMFF1206P2000~3000 Surface Mount Fuses Devices

Reliability Test

Characteristics	Test condition / Methods	Requirement	Test Reference
Voltage Drop	100% In	Deviation between the mean value: <15%	IEC 60127-4
Time/Current	100% In	No fusing, 4 hours min.	UL 248-14
	350% In	≤ 5sec	Refer to Spec.
Temperature Rise	100% In	ΔT <95°C	IEC60127-4
Interrupting Ability	300A/32V DC 200A/48V DC	Without permanent arcing, ignition and bursting of fuse link	UL 248-14 IEC6017-4
Solderability	240°C ± 5°C, 3sec ± 0.5sec	95% coverage min	IEC 60127-4 IEC 60068-2-20 MIL-STD-208
Resistance to Soldering	260°C ± 5°C, 10sec ± 0.5sec	ΔR : <10% Legible appearance	MIL-STD-202 Method 210
Bending Test	Distance between holding points: 90mm Bending: 1 mm; Time: 10 sec	ΔR : <10% No mechanical damages	IEC 60127-4
High Temperature Operating Life	70°C ± 2°C, 60% In, 96 hours	ΔR : <10%; no fusing	MIL-STD-202 Method 108
Low Temperature Storage	-55°C ± 3°C, 96 hours	ΔR : <10%	IEC 60068-2-1
High temperature Storage	125°C ± 2°C, 96 hours	ΔR : <10%	IEC 60068-2-2
Humidity (Steady State)	40°C ± 2°C, 90~95%RH for 1000 hours	ΔR : <10%	MIL-STD-202 Method 103
Salt Spray	5% salt solution, 48 hours	ΔR : <10% Legible appearance	MIL-STD-202 Method 101
Thermal Shock	100 cycles between -65°C / +125°C 60 minutes at each extreme zone	ΔR : <10% No mechanical damage	MIL-STD-202 Method 107

