VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.


UC-65W002
CHARGING CABINET

CE

Item no: 3642281

The product is a charging cabinet designed to securely store and charge multiple laptops or tablets. It features individual charging slots, a lockable front door with a PVC viewing window, and built-in cooling fans to prevent overheating.

The product can deliver max. 65 W to all connected ports at the same time.



TECHNICAL DATA

Input	100-240 V/AC 50/60 Hz
Output	5.0 V/DC 3.0 A; 9.0 V/DC 3 A; 12.0 V/DC 3 A; 15.0 V/DC 3 A; 20.0 V/DC 3.25 A If all 16 ports are connected, the output for each port is max. 65 W Total output: max. 1040 W
Number of USB-C ports®	16
Overload protection	yes
Cooling fan	yes
Charging ports	16
Power cord length	2.6 m
Power cable thickness	1.5 mm^2
Charging bay size (W x H x D)	28 x 273 x 398 mm
Operating conditions	0 to +40 °C, 5-90% RH (non-condensing)
Storage conditions	-20 to +80 °C, 5-90% RH (non-condensing)
Dimensions (W x H x D)	590 x 400 x 422
Weight	22 kg

CONTENTS

Product // 2x sets of keys // 4x M6 x16 pan head screws // 4x wall plugs // 4x rubber feet // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*3642281_V1_0926_en_ds 3300275851 I1/O1 en