

**Infinitely height adjustable
up to 1.60 m**

Fast heat-up time

**Gentle and efficient
method for removing
wrinkles from textiles**



*Vertical steam ironing for
hanging garments*



*Gentle and efficient removal
of wrinkles from textiles*



*3-way adjustable
ironing board*



2in1
Brush attachment / tongs for
the perfect crease on elegant
business trousers or for skirts, as
well as for removing lint

PC-TDC 3128 Textile steamer

Without decoration

- > Steam straightener for steam ironing, smoothing and lint removal
- > Gentle and efficient textile care
 - Gentle smoothing
 - hygienic refreshing
 - Removing lint
 - Neutralise/remove odours
 - Volume/refreshing
 - Also suitable for the care of upholstered furniture, curtains etc.
 - Reduce bacteria/germs
- > Saves time compared to conventional ironing
- > Also suitable for delicate fabrics
- > Fast heat-up time thanks to powerful 1580 W - ready for use in approx. 50 sec.
- > Removable water tank with 1.5 litre capacity capacity
- > Up to 40 min. operating time with one tank filling
- > Infinitely height-adjustable telescopic handle (up to 1.6 m) for customised adjustment to body height and easy storage
- > 5-stage steam boost setting: up to 30 g/min.
- > Vertical steam ironing for hanging garments, curtains etc.
- > Horizontal steam ironing, thanks to adjustable ironing board
- > Anti-drip system
- > Accessories: Textile brush attachment for smoothing and lint removal, ironing board, glove
- > LED display
- > Overheating protection
- > Fire protection
- > 220-240 V, 50/60 Hz, 1580 W



LED-display



*Water tank with 1.5 liters
capacity (removable)*

white-rose	Art. no:	331 280	PU:	20"/40"/HQ container:
	Art. EAN:	4 006 160 312 805	Cable length:	1
	Export carton EAN:	4 006 160 512 403	Device (W x H x D):	336 / 696 / 850
			approx. 1,75 m	470 x 1330 x 400 mm
			Plug type:	Packaging (W x H x D):
			safety plug	366 x 418 x 494 mm