

2620 : Manual Test Pump and Connect

The + product :

EA85 anti-limestone patent: to avoid blockages caused by over-hard water.

Easy to use: for pumping, testing and bleeding with a single button.

Small size for the tightest of locations.

Description

4 pump models for your seal tests (for leak testing on water installations-plumbing, individual central heating, etc.).

Virax EA85 anti-limestone patented system: Prevents blockages due to hard water, or other deposits, on the ball in the piston (50 bar models only).

Plastic tank: light and shock resistant (max.: 4.3 kg).

Accurate result with a 1.6 class manometer. Easier reading with 1 bar grading.

High pressure hydraulic hose (1.5 m). Practical implementation.

Nylon strainer (filter) on intake **to block particles** exceeding 0.1 mm diameter to protect the pump mechanism and the customer's installation against dirt.

Soft Touch® ergonomic lever for working comfortably.


Easy to carry thanks to a lever locking mechanism.

Fluids accepted: water, Glycol (requires rinsing after use), oil (requires rinsing after use).

Connect 5L 50Bar test pump:

Test pump application available on Android/iOS for:

- Monitor the evolution of pressure in real time
- Record the evolution of the pressure over 24 hours.
- Write and transfer an intervention report



References

SKU	Description	Pressure bar	Coupling "	Tank capacity L	kg
262036	Connect manual test pump	50	1/2 - 3/8	5	3,750

Sku	Description	Pressure bar	Coupling "	Tank capacity L	kg
262035	Manual test pump	50	1/2 - 3/8	5	3,650
262015	High volume test pump	50	1/2 - 3/8	10	4,100
262005	High pressure test pump	100	1/2 - 3/8	10	4,290

