

DATASHEET

Waterproof Cable Connector, IP68

Technical data

Item no.	Shape	Poles	Connection	Dimensions (mm)
3686314	T-junction	3	Screwed	101.95 x 84.6
3686315	T-junction	5	Screwed	101.95 x 84.6
3686316	Y-connector	3	Screwed	139.71 x 71.8
3686317	Y-connector	5	Screwed	139.7 x 71.8

Item no.	Rated Output	Wiring Range (Cross section)	Outer cable diameter
3686314	450 V/AC 32 A	0.5 - 4.0 mm ²	4-8 / 8-12 / 10-14 mm
3686315	450 V/AC 32 A	0.5 - 4.0 mm ²	4-8 / 8-12 / 10-14 mm
3686316	450 V/AC 32 A	0.5 - 4.0 mm ²	4-8 / 8-12 / 10-14 mm
3686317	450 V/AC 32 A	0.5 - 4.0 mm ²	4-8 / 8-12 / 10-14 mm

Protection classIP68
 MaterialFire and flame retardant UL94V-2
 ColorBlack
 Nut sizeM25
 Operating Temperature-40 to +105 °C

Features


- Built-in rubber ring and clamping nut
- IP68
- UL94V-2

Item no.: 3686314



All measurements in mm

Wiring Steps




Item no.: 3686315




All measurements in mm

Wiring Steps




Item no.: 3686316




All measurements in mm

Wiring Steps



Item no.: 3686317



All measurements in mm

Wiring Steps

