


ENERGIZER A95

D



Industry Standard Dimensions




General Information

Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	ANSI-13A, IEC-LR20
Nominal Voltage:	1.5 volts
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Typical Weight:	139 grams
Typical Volume:	56 cubic centimeters
Shelf Life:	10 years at 21°C
Terminal:	Flat Contact

Performance Comparison

A95 vs. Typical Carbon Zinc (D) at 21°C



Industry Standard Testing Protocol

Device Selection Guide:

Portable Stereo



Toy



Lighting



Radio



Battery Selection Indicator

High Drain
Devices

Moderate Drain
Devices

Low Drain
Devices

Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
Contents herein do not constitute a warranty and are for reference only.