


Heat-Shrink-Tube Boxes 2:1 Black, 5m / 10m Item-No.: 26CA767 ... 26CA762



These high-quality shrinking tubes are particularly suitable for service workshops, electronics technicians and applications with a high demand for shrink tubing. The black heat-shrink tube is wound onto a cardboard reel inside the dispenser box and can therefore be cut to length individually. Various available nominal diameters open up a wide range of applications. The standard version with a shrink ratio of 2:1 without internal adhesive is ideal for most applications.

Technical Specifications

Material: PE • Shrink ratio: 2:1 • Shrink temperature (min.): 90 °C • Shrink temperature (max.): 125 °C • Operating temperature: -40 °C ... +125 °C • Tensile strength (min.): 10.4 MPa • Dielectric strength 15 kV/mm (30 sec.) • Rated voltage: 600 V • Elongation break: min. 300% • Color: Black.

Versions

Item-No.	Description	Diameter	Color	Content	EAN/GTIN
26CA767	Shrinking-Tube Black 2:1 (Ø 1 mm)	1 mm	Black	10 m	4262511626261
26CA768	Shrinking-Tube Black 2:1 (Ø 2 mm)	2 mm	Black	10 m	4262511626278
26CA769	Shrinking-Tube Black 2:1 (Ø 4 mm)	4 mm	Black	10 m	4262511626285
26CA770	Shrinking-Tube Black 2:1 (Ø 6 mm)	6 mm	Black	10 m	4262511626292
26CA771	Shrinking-Tube Black 2:1 (Ø 8 mm)	8 mm	Black	10 m	4262511626308
26CA772	Shrinking-Tube Black 2:1 (Ø 10 mm)	10 mm	Black	10 m	4262511626315
26CA773	Shrinking-Tube Black 2:1 (Ø 12 mm)	12 mm	Black	10 m	4262511626322
26CA774	Shrinking-Tube Black 2:1 (Ø 14 mm)	14 mm	Black	10 m	4262511626339
26CA775	Shrinking-Tube Black 2:1 (Ø 16 mm)	16 mm	Black	10 m	4262511626346
26CA776	Shrinking-Tube Black 2:1 (Ø 18 mm)	18 mm	Black	5 m	4262511626353
26CA777	Shrinking-Tube Black 2:1 (Ø 20 mm)	20 mm	Black	5 m	4262511626360
26CA778	Shrinking-Tube Black 2:1 (Ø 25 mm)	25 mm	Black	5 m	4262511626377
26CA779	Shrinking-Tube Black 2:1 (Ø 30 mm)	30 mm	Black	5 m	4262511626384
26CA780	Shrinking-Tube Black 2:1 (Ø 35 mm)	35 mm	Black	5 m	4262511626391
26CA781	Shrinking-Tube Black 2:1 (Ø 40 mm)	40 mm	Black	5 m	4262511626407
26CA782	Shrinking-Tube Black 2:1 (Ø 50 mm)	50 mm	Black	5 m	4262511626414