

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry.

We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

BS-802 DUAL CAMERA PROBE



Item no. 3733404

FEATURES

HD (1280 x 720) dual camera // Compatible with B/N 3553223 3553224 3553225 // 1/9" HD CMOS sensor

PACKAGE CONTENTS

HD dual camera probe // Operating instructions

TECHNICAL DATA

Cable Type	Rigid
Camera Head Dia.	5.5 mm
Resolution	1280 x 720p (Front & Side)
Sensor	1/9" HD CMOS
Field of View (FOV)	87°
Fixed Focus	Front: 35 - 60 mm, Side: 20 - 50 mm
Min. bending radius	45 mm
LEDs	6+1 adjustable (Front & Side)
LED brightness (at a distance of 35 mm)	Front: 580 ±150 lux Side: 1500 ±150 lux
IP Rating	IP67
Operating temperature	0 to +45 °C
Operating humidity	15 – 85 % RH
Storage temperature	-10 to +50 °C
Storage humidity	15 – 85 % RH
Length	1 m
Weight	92 g

