




Heat-Shrink-Tube Boxes 4:1 with Glue Item-No.: 25CA725 ... 25CA734



These high-quality shrink sleeves are particularly suitable for service workshops, electronics technicians and applications with a high demand for shrink tubing. The black heat-shrink tube is wound onto a cardboard

reel inside the carton dispenser and can therefore be cut to length individually. Various available nominal diameters open up a wide range of applications. The version with inner glue and a very high shrink ratio of 4:1 is ideal for applications with high demands on the wrapping.

Technical Specifications

Material: PE • Shrink ratio: 4:1 • Diameter before shrinking: 4 mm ... 52 mm • Hot melt adhesive • Shrink temperature (min.): +80 °C • Shrink temperature (max.): +125 °C • Operating temperature: -40 °C ... +125 °C • Double-wall-technology • Tensile strength (min.): 10.4 MPa • Dielectric strength 15 kV/mm (30 sec.) • Rated voltage: 600 V • Axial shrinkage: <8% • Color: Black.

Versions

Item-No.	Description	Diameter	ø after shrinking	Content	EAN/GTIN
25CA725	Shrinking tube ø 4 mm 4:1 with glue 10 m	4 mm	1 mm	10 m	4262511625110
25CA726	Shrinking tube ø 6 mm 4:1 with glue 5 m	6 mm	1.5 mm	5 m	4262511625127
25CA727	Shrinking tube ø 8 mm 4:1 with glue 5 m	8 mm	2 mm	5 m	4262511625134
25CA728	Shrinking tube ø 12 mm 4:1 with glue 5 m	12 mm	3 mm	5 m	4262511625141
25CA729	Shrinking tube ø 16 mm 4:1 with glue 5 m	16 mm	4 mm	5 m	4262511625158
25CA730	Shrinking tube ø 20 mm 4:1 with glue 5 m	20 mm	5 mm	5 m	4262511625165
25CA731	Shrinking tube ø 24 mm 4:1 with glue 5 m	24 mm	6 mm	5 m	4262511625172
25CA732	Shrinking tube ø 32 mm 4:1 with glue 5 m	32 mm	8 mm	5 m	4262511625189
25CA733	Shrinking tube ø 40 mm 4:1 with glue 5 m	40 mm	10 mm	5 m	4262511625196
25CA734	Shrinking tube ø 52 mm 4:1 with glue 5 m	52 mm	13 mm	5 m	4262511625202