



TOOLCRAFT

DATASHEET


Lead Free Solder Bath

Item no. 3593716 (TC-8911C)

Item no. 2361151 (LTB-911A)



Item no 3593716



Item no 2361151

Technical data

Item no 3593716

Input voltage / current.....	220 - 240 V/AC, 50 Hz
Power consumption.....	max. 200 W
Fuse.....	3.15 A, VDE, Type: FSD
Temperature range	150 - 420 °C
Melting time	approx. 8 - 25 min at 420 °C: 8 mins to reach 200 °C 25 mins to reach 420 °C
Melt capacity.....	max. 300 g
Protection class	I
Material.....	Pot: Iron Pot coating: Titanium alloy Housing: Iron Housing coating: Lacquer
Operating conditions.....	-10 to +50 °C, 10 – 90 % RF (non-condensing)
Storage conditions	-20 to +60 °C, 10 – 90 % RF (non-condensing)
Dimensions (W x H x D)	110 x 80 x 195 mm
Inner dimensions crucible (Ø x H)	50 x 23 mm
Weight	1 kg

Item no 2361151

Input voltage / current.....	220 - 240 V/AC, 50 Hz
Power consumption.....	max. 300 W
Fuse.....	3.15 A, VDE, Type: FSD
Temperature range	200 - 480 °C
Melting time	approx. 8 - 25 min at 480 °C: 8 mins to reach 200 °C 25 mins to reach 480 °C
Melt capacity.....	max. 1350 g
Protection class	I
Material.....	Pot: Iron Pot coating: Titanium alloy Housing: Iron Housing coating: Lacquer
Operating conditions.....	-10 to +50 °C, 10 – 90 % RF (non-condensing)
Storage conditions	-20 to +60 °C, 10 – 90 % RF (non-condensing)
Dimensions (W x H x D)	161 x 95 x 245 mm
Inner dimensions crucible (Ø x H)	80 x 41 mm
Weight	1.97 kg