
DATASHEET

Sticky Mat



Product Structure



	3752520	3752521	3752522
Color	Blue	Blue	Blue
Layers	30 layers per mat	30 layers per mat	30 layers per mat
Film thickness	45 µm	45 µm	45 µm
Dimensions (W x H x D)	600 x 15 x 900 mm	1150 x 15 x 450 mm	1140 x 15 x 650 mm
Weight	0.72 kg	0.8 kg	1.03 kg

Electrical properties

Surface resistance	10^9 to 10^{11} Ω (Rectified from 9-11 Ω) valid for approx. 3 months

Environment and storage

Operating conditions	0 to +40 °C, 0 - 85 % RH (non-condensing)
Storage conditions	-20 to +40 °C, 0 - 85 % RH (non-condensing)
Shelf life	8 months

Material specifications

Base material	Low-density polyethylene (LDPE)
Adhesive	Water-based acrylic, anti-static coating


Mechanical properties

Longitudinal tensile strength	≥10 MPA
Lateral tensile strength	≥8 MPA
Longitudinal elongation at break	≥150 %
Lateral elongation at break	≥200 %
Initial adhesion (G/IN2)	500 (LOOPTACK)
180° peel strength (SS.G/25MM)	380

Instructions




1. Tear off the bottom film




2. The bottom surface is pasted on the ground, etc., and the attachment surface is smoothed by hand




3. Tear off the top layer of film from the corner label



4. After using one layer, tear off the label, tear off this layer completely, and use the next







This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

Copyright 2026 by Conrad Electronic SE.