VOLTCRAFT

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

UC-30W002
30 W GAN CHARGER

CE

Item no: 3778456

The product is a GaN charger with fast charge support.



TECHNICAL DATA

Data according to EU regulation 2019/1782

Manufacturer	Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau
Commercial registration number	HRB 3896
Model identifier	UC-30W002
Input voltage	110 - 240 V/AC
Input AC frequency	50 / 60 Hz
Output voltage Output current Output power	**USB-C®:** 5.0 V/DC, 3.0 A, max. 15.0 W; 9.0 V/DC, 3.0 A, max. 27.0 W; 12.0 V/DC, 2.5 A, max. 30.0 W; 15.0 V/DC, 2.0 A, max. 30.0 W; 20.0 V/DC, 1.5 A, max. 30.0 W; **USB-A:** 5.0 V/DC, 3.0 A, max. 15.0 W; 9.0 V/DC, 2.0 A, max. 18.0 W; 12.0 V/DC, 1.5 A, max. 18.0 W;
Average active efficiency	87.5 %
Efficiency at low load (10 %)	76.0 %
No-load power consumption	0.07 W

Environment

Operating conditions	0 to +40 °C, 5 - 90 % RH (non-condensing)
Storage conditions	-35 to +70 °C, 0 - 90 % RH (non-condensing)

Others

PPS	5.0 - 11 V/DC, 2.7 A, max. 29.7 W 5.0 - 16 V/DC, 1.85 A, max. 29.6 W
Dimensions (W x H x D) (approx.)	approx. 36 x 15 x 81 mm
Weight (approx.)	55 g

CONTENTS

Product // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92242 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE.

*3778456_V1_0926_en_ds 9007202528129675 I2/O1 en