

## ANTENNAS | XPOL-1- 5G+ SERIES

# X-POLARISED, OMNI-DIRECTIONAL, 2x2 MIMO 5G ANTENNA

410 – 6000 MHz, 6 dBi



|                                                                                                                |                         |                        |                          |              |           |
|----------------------------------------------------------------------------------------------------------------|-------------------------|------------------------|--------------------------|--------------|-----------|
| <br>410 – 470 MHz<br>617 – 960 MHz<br>1427 – 1517 MHz<br>1710 – 2700 MHz<br>3300 – 4200 MHz<br>4400 – 6000 MHz | <br>6 dBi               | <br>Increase<br>X Mb/s | <br>Omni-<br>Directional | <br>4G LTE   | <br>5G    |
| <br><b>BAND 71</b>                                                                                             | <br><b>3.5 GHz CBRS</b> | <br>-40°C to +80°C     | <br>Fire Resistant       | <br>2x2 MIMO | <br>IP 65 |

APPLICATION AREAS

Urban

Commercial & Industrial

- Ultra-Wideband cellular antennas from 410 to 6000 MHz
- Cross-polarised antennas for improved performance
- Omni-directional antenna with a low-profile design
- High gain for the antenna size
- 2x2 MIMO 4G/5G antenna for higher data throughputs
- Versatile mounting options for ease of installation
- Weather, dust, and vandal-resistant enclosure (IP 65)

## Product Overview

The XPOL-1-5G+ is Poynting's third generation "V3" of this very popular Cross Polarised (XPOL), cellular band, 2x2 or 4x4 MIMO antenna. The antenna has been completely redesigned from previous generations, featuring an all-new enclosure and high-performing antenna design. The XPOL-1-5G+ is now ultra-wideband, covering a broad frequency range from 410 to 6000 MHz. This allows it to be utilized across different cellular operators and technologies, and it is ready for future cellular technologies up to 6GHz for 5G applications. The 2x2 MIMO antenna option offers a 2-in-1 solution that includes two cross-polarized cellular antennas. Under most conditions, these cross-polarized antennas can potentially double your data rates.

The XPOL-1-5G+ antenna delivers exceptional performance with a peak gain of 6 dBi, nearly double the peak gain of the previous version (V2). This improvement enables superior signal strength and extended coverage in Fixed Wireless Access (FWA) deployments. The radiation patterns of this antenna are omni-directional and exceptionally well controlled, further enhancing its performance. This makes the antenna perfect for various application areas, such as urban, suburban, and commercial, to achieve the best possible coverage over a large area. The robust mechanical enclosure design makes the antenna weather, dust, and vandal resistant, granting it an IP65 rating, suitable for outdoor environments.

## Features

- Ultra-wideband coverage from 410 to 6000 MHz
- X-Polarised 2x2 MIMO Antenna
- Wall, Pole, or Window mountable
- Low-profile and rugged mechanical design with an IP65 rating
- High pattern consistency across bands for 4G/5G carrier aggregation


## Application Areas

- Outdoor antenna for Fixed Wireless Access (FWA)
- Homes and small offices in both urban and suburban environments
- Small to medium-sized businesses across various commercial and industrial sectors such as retail outlets, petrol stations, guesthouses, banks, etc.
- Temporary offices on construction sites
- Serve as a reliable backup connectivity option for locations that use fibre or Starlink as their primary internet connection



Frequency Bands

The XPOL-1-5G+ is an 5G antenna that works from | 410 – 470 MHz | 617 – 960 MHz | 1427 – 1517 MHz | 1710 – 2700 MHz | 3300 – 4200 MHz | and | 4400 – 6000 MHz |



Indicates the 5G/LTE bands on which XPOL-1-5G+ works

Indicates the WI-FI bands on which XPOL-1-5G+ works

Antenna Overview

|                   | <div>5G<br/>LTE</div> |
|-------------------|-----------------------|
| Number of Ports   | 2                     |
| SISO / MIMO       | 2x2 MIMO              |
| Frequency Bands   | 410 – 6000 MHz        |
| Polarisation      | Cross Polarised       |
| Peak Gain         | 6 dBi                 |
| Coax Cable Type   | HDF 195               |
| Coax Cable Length | 5m                    |
| Connector Type    | SMA (M)               |

\*The coax cables & connectors are factory mounted to the antenna

Electrical Specifications

|                      |                                                                                                                                                                 |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Frequency Bands:     | 410 – 470 MHz<br>617 – 960 MHz<br>1427 – 1517 MHz<br>1710 – 2700 MHz<br>3300 – 4200 MHz<br>4400 – 6000 MHz                                                      |
| Gain (Max):          | -4 dBi @ 410 – 470 MHz<br>2 dBi @ 617 – 960 MHz<br>2.5 dBi @ 1427 – 1517 MHz<br>5 dBi @ 1710 – 2700 MHz<br>6 dBi @ 3300 – 4200 MHz<br>5.5 dBi @ 4400 – 6000 MHz |
| VSWR:                | ≤2:1<br>across 90% of the bands                                                                                                                                 |
| Feed Power Handling: | 10 W                                                                                                                                                            |
| Input Impedance:     | 50 Ohm (nominal)                                                                                                                                                |
| Polarisation:        | Cross Polarised                                                                                                                                                 |
| Coax Cable Loss:     | 0.385 dB/m @ 900 MHz<br>0.507 dB/m @ 1500 MHz<br>0.565 dB/m @ 1800 MHz<br>0.788 dB/m @ 3000 MHz                                                                 |
| DC Short:            | Yes, path to ground                                                                                                                                             |

Product Box Contents

|                   |                                                             |
|-------------------|-------------------------------------------------------------|
| Antenna:          | A-XPOL-0001-V3-21                                           |
| Mounting Bracket: | Pole/Wall mounting bracket and window suction cups included |

Ordering Information

|                     |                   |
|---------------------|-------------------|
| Commercial Name:    | XPOL-1-5G+        |
| Order Product Code: | A-XPOL-0001-V3-21 |
| EAN Number:         | 6009710929216     |

Mechanical Specifications

|                      |                                                |
|----------------------|------------------------------------------------|
| Product Dimensions   | 246 mm x 157 mm x 88 mm<br>(including bracket) |
| Packaged Dimensions: | 271 mm x 191 mm x 120 mm                       |
| Weight:              | 0.7 Kg                                         |
| Packaged Weight:     | 1.05 Kg                                        |
| Radome Material:     | UV Stable ASA                                  |
| Radome Colour:       | Brilliant White<br>Pantone P 179-1 C           |
| Mounting Type:       | Wall, pole, and window mount                   |


Environmental Specifications, Certification & Approvals

|                                          |                                                     |
|------------------------------------------|-----------------------------------------------------|
| Wind Survival:                           | ≤250 km/h<br>*Except for window mount configuration |
| Temperature Range (Operating):           | -40°C to +80°C                                      |
| Environmental Conditions:                | Outdoor/Indoor                                      |
| Water Ingress Protection Ratio/Standard: | IP 65                                               |
| Salt Spray:                              | MIL-STD 810G/ASTM B117                              |
| Operating Relative Humidity:             | Up to 98%                                           |
| Storage Humidity:                        | 5% to 95% - non-condensing                          |
| Storage Temperature:                     | -40°C to +80°C                                      |
| Enclosure Flammability Rating:           | UL 94-HB                                            |
| Impact Resistance:                       | IK 10                                               |
| Product Safety & Environmental:          | Complies with CE and RoHS standards                 |



Antenna Performance Plots

VSWR




Voltage Standing Wave Ratio (VSWR)\*

VSWR is a measure of how efficiently radio-frequency power is transmitted from a power source, through a transmission line, into a load. In an ideal system, 100% of the energy is transmitted which corresponds to a VSWR of 1:1.

The XPOL-1-5G+ delivers superior performance across all bands with a VSWR of  $\leq 2:1$  across 90% of the bands.

\*VSWR measured with a 5m low loss cable.


ISOLATION



Isolation

Isolation is a measure of how much energy from one port leaks into another port undesirably. Isolation of 0 dB between 2 ports means that there is no isolation and the energy from 1 port excitation is visible on another port. Isolation of -30 dB or more means that <0.1% of 1 port's energy is leaked into another. A good isolation is under -10 dB.

GAIN (EXCLUDING CABLE LOSS)



Gain\* in dBi


6 dBi is the peak gain across all bands from 410 – 6000 MHz

|                         |         |
|-------------------------|---------|
| Gain @ 410 – 470 MHz:   | -4 dBi  |
| Gain @ 617 – 960 MHz:   | 2 dBi   |
| Gain @ 1427 – 1517 MHz: | 2.5 dBi |
| Gain @ 1710 – 2700 MHz: | 5 dBi   |
| Gain @ 3300 – 4200 MHz: | 6 dBi   |
| Gain @ 4400 – 6000 MHz: | 5.5 dBi |


\*Antenna gain measured with polarisation aligned standard antenna

## Radiation Patterns – Cell 1 Main


**Azimuth: 410 – 470 MHz**




**Elevation: 410 – 470 MHz**




**Azimuth: 617 – 960 MHz**




**Elevation: 617 – 960 MHz**




**Azimuth: 1427 – 1517 MHz**




**Elevation: 1427 – 1517 MHz**




**Azimuth: 1710 – 2170 MHz**




**Elevation: 1710 – 2170 MHz**




**Azimuth: 2300 – 2700 MHz**




**Elevation: 2300 – 2700 MHz**




**Azimuth: 3300 – 3800 MHz**




**Elevation: 3300 – 3800 MHz**




**Azimuth: 3900 – 4200 MHz**




**Elevation: 3900 – 4200 MHz**




**Azimuth: 4400 – 5000 MHz**




**Elevation: 4400 – 5000 MHz**



**Azimuth: 5000 – 6000 MHz**




**Elevation: 5000 – 6000 MHz**




## Radiation Patterns – Cell 2 Main


Azimuth: 410 – 470 MHz




Elevation: 410 – 470 MHz




Azimuth: 617 – 960 MHz




Elevation: 617 – 960 MHz




Azimuth: 1427 – 1517 MHz




Elevation: 1427 – 1517 MHz




Azimuth: 1710 – 2170 MHz




Elevation: 1710 – 2170 MHz




Azimuth: 2300 – 2700 MHz




Elevation: 2300 – 2700 MHz




Azimuth: 3300 – 3800 MHz




Elevation: 3300 – 3800 MHz




Azimuth: 3900 – 4200 MHz




Elevation: 3900 – 4200 MHz




Azimuth: 4400 – 5000 MHz




Elevation: 4400 – 5000 MHz



Azimuth: 5000 – 6000 MHz




Elevation: 5000 – 6000 MHz




Combined Radiation Patterns – Cell 1 and Cell 2 Main


Azimuth: 410 – 470 MHz




Elevation: 410 – 470 MHz




Azimuth: 617 – 960 MHz




Elevation: 617 – 960 MHz




Azimuth: 1427 – 1517 MHz




Elevation: 1427 – 1517 MHz




Azimuth: 1710 – 2170 MHz




Elevation: 1710 – 2170 MHz




Azimuth: 2300 – 2700 MHz




Elevation: 2300 – 2700 MHz




**Azimuth: 3300 – 3800 MHz**




**Elevation: 3300 – 3800 MHz**




**Azimuth: 3900 – 4200 MHz**




**Elevation: 3900 – 4200 MHz**




**Azimuth: 4400 – 5000 MHz**




**Elevation: 4400 – 5000 MHz**



**Azimuth: 5000 – 6000 MHz**




**Elevation: 5000 – 6000 MHz**



\*Combined Patterns are for MIMO operation illustration

Technical Drawings



## Mounting Options



### Pole Mount

Pole mounting using the provided bracket and pipe clamp



### Wall Mount

Wall mounting using provided bracket and knock-in screws



### Window Mount

Window mounting using the provided suction cups

---

## Additional Accessories

Extension Cables: Up to 10m HDF 195  
Various connectors available  
Installation poles and brackets available

See accessories technical specifications on [www.poynting.tech](http://www.poynting.tech)

---

## CONTACT POYNTING

### Poynting Antennas (Pty) Ltd - Head Office

Unit 4, N1 Industrial Park,  
Landmarks Avenue,  
Samrand, 0157, South Africa

**Phone:** +27 (0) 12 657 0050

**E-mail:** [info@poynting.tech](mailto:info@poynting.tech)

**International Email:** [sales-global@poynting.tech](mailto:sales-global@poynting.tech)

### Poynting Europe

Regus Business Center Neue Messe Riem  
Kronstadter Straße 4  
81677 München  
Germany

**Phone:** +49 89 7453 9002

**E-mail:** [sales-europe@poynting.tech](mailto:sales-europe@poynting.tech)

### Poynting USA

1804 Owen Court, Suite 104,  
Mansfield,  
TX 76063  
USA

**Phone:** +1 817 533-8130

**E-mail:** [sales-us@poynting.tech](mailto:sales-us@poynting.tech)